

Miniature Circuit Breakers Curve C

1.3 Up to 10kA - S200 Series

Miniature Circuit Breaker S200 (C - Curve / Curve 2) Up to 10kA (VC8036)

Function: Protection and control of circuits against overloads and short-circuits, protection for resistive and inductive loads with low inrush current.

Application: Domestic, commercial and industrial



S201 Single Pole MCB Din Rail Mount (230 VAC - 60 VDC)

Type	Order Code	No. of Poles (17.5 mm)	Rated Current (A)	Rated kA at 230 VAC (Icu)	Rated kA at 230 VAC (Ics)	Units Per Pack	Price Per Unit Excl. VAT
S201-C2	2CDS251001R0024	1	2	10	7.5	10	R190,98
S201-C6	2CDS251001R0064	1	6	10	7.5	10	R140,89
S201-C10	2CDS251001R0104	1	10	10	7.5	10	R140,89
S201-C16	2CDS251001R0164	1	16	10	7.5	10	R140,89
S201-C20	2CDS251001R0204	1	20	10	7.5	10	R140,89
S201-C25	2CDS251001R0254	1	25	10	7.5	10	R145,59
S201-C32	2CDS251001R0324	1	32	10	7.5	10	R145,59
S201-C40	2CDS251001R0404	1	40	10	7.5	10	R145,59
S201-C50	2CDS251001R0504	1	50	10	7.5	10	R164,37
S201-C63	2CDS251001R0634	1	63	10	7.5	10	R170,64
S201-C80	2CDS251001R0804	1	80	6	6	10	R519,85
S201-C100	2CDS251001R0824	1	100	6	6	10	R519,85



S202 Double Pole MCB Din Rail Mount (400 VAC - 125 VDC)

Type	Order Code	No. of Poles (35 mm)	Rated Current (A)	Rated kA at 400 VAC (Icu)	Rated kA at 400 VAC (Ics)	Units Per Pack	Price Per Unit Excl. VAT
S202-C2	2CDS252001R0024	2	2	10	7.5	5	R581,97
S202-C6	2CDS252001R0064	2	6	10	7.5	5	R494,28
S202-C10	2CDS252001R0104	2	10	10	7.5	5	R452,02
S202-C16	2CDS252001R0164	2	16	10	7.5	5	R452,02
S202-C20	2CDS252001R0204	2	20	10	7.5	5	R452,02
S202-C25	2CDS252001R0254	2	25	10	7.5	5	R517,47
S202-C32	2CDS252001R0324	2	32	10	7.5	5	R517,47
S202-C40	2CDS252001R0404	2	40	10	7.5	5	R517,47
S202-C50	2CDS252001R0504	2	50	10	7.5	5	R550,96
S202-C63	2CDS252001R0634	2	63	10	7.5	5	R550,96
S202-C80	2CDS252001R0804	2	80	6	6	5	R1 299,64
S202-C100	2CDS252001R0824	2	100	6	6	5	R1 299,64



S203 Triple Pole MCB Din Rail Mount (400 VAC)

Type	Order Code	No. of Poles (52.5 mm)	Rated Current (A)	Rated kA at 400 VAC (Icu)	Rated kA at 400 VAC (Ics)	Units Per Pack	Price Per Unit Excl. VAT
S203-C2	2CDS253001R0024	3	2	10	7.5	1	R931,15
S203-C6	2CDS253001R0064	3	6	10	7.5	1	R701,63
S203-C10	2CDS253001R0104	3	10	10	7.5	1	R675,75
S203-C16	2CDS253001R0164	3	16	10	7.5	1	R675,75
S203-C20	2CDS253001R0204	3	20	10	7.5	1	R675,75
S203-C25	2CDS253001R0254	3	25	10	7.5	1	R683,37
S203-C32	2CDS253001R0324	3	32	10	7.5	1	R683,37
S203-C40	2CDS253001R0404	3	40	10	7.5	1	R683,37
S203-C50	2CDS253001R0504	3	50	10	7.5	1	R694,02
S203-C63	2CDS253001R0634	3	63	10	7.5	1	R712,28
S203-C80	2CDS253001R0804	3	80	6	6	1	R1 749,52
S203-C100	2CDS253001R0824	3	100	6	6	1	R1 749,52

Note:

Also available in B and K curve. Contact ABB for more information. Icu/Ics rating according to IEC 60947-2