



The Leading Manufacturer  
of Non-Marring,  
Non-Sparking Hammers,  
Proudly Made in the USA,  
Since 1956.



### STANDARD DEAD BLOW HAMMERS

ITEM #	WEIGHT [OZ/LBS/KGS]	HANDLE LENGTH [IN/MM]	OVERALL LENGTH [IN/MM]	STRIKING FACE DIAMETER [IN]	HEAD LENGTH [IN]
ABC2DB	26 oz/1.6 lbs/0.74 kg	10.5"/267mm	12.75"/324mm	2.00"	4.125"
ABC3DB	45 oz/2.8 lbs/1.28 kg	12"/305mm	14.375"/365mm	2.25"	4.625"
ABC4DB	53 oz/3.3 lbs/1.50 kg	12.5"/318mm	15.25"/387mm	2.75"	5.375"



### SLEDGE DEAD BLOW HAMMERS

ITEM #	WEIGHT [OZ/LBS/KGS]	HANDLE LENGTH [IN/MM]	OVERALL LENGTH [IN/MM]	STRIKING FACE DIAMETER [IN]	HEAD LENGTH [IN]
ABC7DB	88 oz/5.5 lbs/2.49 kg	16.5"/419mm	20"/508mm	2.75"	7"
ABC10DB	144 oz/9.0 lbs/4.08 kg	26"/660mm	30"/762mm	2.75"	7"
ABC12DB	168 oz/10.5 lbs/4.76 kg	26"/660mm	30"/762mm	3.25"	8"
ABC14DB	192 oz/12.0 lbs/5.44 kg	32"/813mm	36"/914mm	3.25"	8"

## APPLICATIONS/INDUSTRIES

Agriculture  
Aircraft Maintenance  
Assembly Work  
Automotive  
Custom Fabrication  
Construction

Electrical  
Fire/Public Safety  
Foundry Operations  
Grain Elevators  
HVAC  
Heavy Duty Truck & Equipment

Landscaping  
Log/Timber Home Building  
Machine Shop  
Machinery Repair  
Marine  
Motorcycle Shop

Pipeline/Oil Field  
Plumbing  
Railroads  
Shipyards  
Tractor/Farm Equipment  
Waste Treatment Plants