



Class 1, Div 2, Low Voltage Distribution Transformer - Single Phase, 600 - 120V/240V, 2kVA

By Acme Electric
Catalog # [T1002K0200CSH](#)



Class 1, Div 2, Low Voltage Distribution Transformer - Single Phase, 600 - 120V/240V, 2kVA

Features

- Class 1 Div. 2, Groups A, B, C, D
- For Hazardous Locations
- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

General

Catalog Number	T1002K0200CSH
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Secondary Voltage	120/240 V
UL Insulation Class	180°C
Winding Material	CU
kVA	2

Dimensions

Dimensions	5.13 in x 5.5 in x 13 in
Height	13 in

Length	5.13 in
Weight	38 lb
Width	5.5 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	600 V

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Nema Rating	NEMA 3R
UL Standard	UL 506

Product Assets

- [Brochures - Encapsulated Transformers for Hazardous Locations Class I, Div. 2](#)
- [SDS - HCC SDS](#)
- [Specifications - T1002K0200CSH](#)
- [Video - Encapsulated Transformers for Hazardous Locations Class I Div 2](#)