



Class 1, Div 2, Low Voltage Distribution Transformer - Single Phase, 120/208/240/277 - 120/240V, 2kVA

By Acme Electric  
Catalog # T1002K0220CSH

Class 1, Div 2, Low Voltage Distribution Transformer - Single Phase, 120/208/240/277 - 120/240V, 2kVA

Features

- Class 1 Div. 2, Groups A, B, C, D
- For Hazardous Locations
- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

Specifications

|                          |                      |
|--------------------------|----------------------|
| Nema Rating              | NEMA 3R              |
| UL Standard              | UL 506               |
| Buy America(n) Qualified | Contact Manufacturer |
| UL Insulation Class      | 180°C                |

Configuration

|                      |          |
|----------------------|----------|
| Electrostatic Shield | Shielded |
|----------------------|----------|

Current

|                   |                   |
|-------------------|-------------------|
| Frequency Rating  | 60 Hz             |
| Primary Voltage   | 120/208/240/277 V |
| kVA               | 2.0               |
| Secondary Voltage | 120/240 V         |



Dimensions

|            |                          |
|------------|--------------------------|
| Weight     | 37 lb.                   |
| Height     | 13 in                    |
| Width      | 5.5 in                   |
| Length     | 5.13 in                  |
| Dimensions | 5.13 in x 5.5 in x 13 in |

General

|                  |              |
|------------------|--------------|
| Material type    | ZFIN         |
| Mounting Type    | Wall         |
| UPC              | 047503021897 |
| Winding Material | CU           |
| Construction     | Encapsulated |

Logistics

|                 |    |
|-----------------|----|
| Pallet Quantity | 16 |
| Carton Quantity | 1  |

Operational

|                      |                     |
|----------------------|---------------------|
| Max Temperature Rise | 115 Degrees Celsius |
|----------------------|---------------------|