



Class 1, Div 2, Low Voltage Distribution Transformer - Single Phase, 277/480 - 208/277V, 5kVA

By Acme Electric
Catalog # [T1005K0270CSH](#)

Class 1, Div 2, Low Voltage Distribution Transformer - Single Phase, 277/480 - 208/277V, 5kVA



Features

- Class 1 Div. 2, Groups A, B, C, D
- For Hazardous Locations
- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

Specifications

Nema Rating	NEMA 3R
UL Standard	UL 506
Buy America(n) Qualified	Contact Manufacturer
UL Insulation Class	180°C

Configuration

Electrostatic Shield	Shielded
----------------------	----------

Current

Frequency Rating	60 Hz
Primary Voltage	277/480 V
kVA	5.0
Secondary Voltage	208/277 V

Dimensions

Weight	80 lb.
Height	14.38 in
Width	10.31 in
Length	7.13 in
Dimensions	7.13 in x 10.31 in x 14.38 in

General

Material type	ZFIN
Mounting Type	Wall
UPC	047503022078
Winding Material	CU
Construction	Encapsulated

Logistics

Pallet Quantity	1
Carton Quantity	1

Operational

Max Temperature Rise	115 Degrees Celsius
----------------------	---------------------