



Class 1, Div 2, Low Voltage Distribution Transformer - Single Phase, 600 - 120V/240V, 7.5kVA

By Acme Electric
Catalog # [T1007K0201CSH](#)

Class 1, Div 2, Low Voltage Distribution Transformer - Single Phase, 600 - 120V/240V, 7.5kVA

Features

- Class 1 Div. 2, Groups A, B, C, D
- For Hazardous Locations
- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

General

BNFC Taps	2
Catalog Number	T1007K0201CSH
Construction	Encapsulated
Electrostatic Shield	Shielded
Material Type	ZFIN
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Secondary Voltage	120/240 V
Taps % Steps	5%
UL Insulation Class	180°C
Winding Material	AL
kVA	7.5

Dimensions

Dimensions	10.84 in x 13.5 in x 15.19 in
Height	15.19 in



Length	10.84 in
Weight	115 lb
Width	13.5 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	600 V

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Nema Rating	NEMA 3R
UL Standard	UL 506

Logistics

Carton Quantity	1
-----------------	---

Product Assets

[Brochures - Encapsulated Transformers for Hazardous Locations Class I, Div. 2](#)
[SDS - HCC SDS](#)
[Specifications - T1007K0201CSH](#)
[Video - Encapsulated Transformers for Hazardous Locations Class I Div 2](#)