



Class 1, Div 2, Low Voltage Distribution Transformer - Single Phase, 240X480 - 120/240V, 10kVA

By Acme Electric
Catalog # [T1010K0193CSH](#)

Class 1, Div 2, Low Voltage Distribution Transformer - Single Phase, 240X480 - 120/240V, 10kVA

Features

- Class 1 Div. 2, Groups A, B, C, D
- For Hazardous Locations
- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

Specifications

Nema Rating	NEMA 3R
UL Standard	UL 506
Buy America(n) Qualified	Contact Manufacturer
UL Insulation Class	180°C

Configuration

Electrostatic Shield	Shielded
ANFC Taps	2

Current

Frequency Rating	60 Hz
Primary Voltage	240 X 480 V
kVA	10.0
Secondary Voltage	120/240 V



Dimensions

Weight	125 lb.
Height	15.19 in
Width	13.5 in
Length	10.84 in
Dimensions	10.84 in x 13.5 in x 15.19 in

General

Material type	ZFIN
Taps % Steps	2.5%
Mounting Type	Wall
Winding Material	AL
BNFC Taps	4
Construction	Encapsulated

Logistics

Pallet Quantity	6
Carton Quantity	1

Operational

Max Temperature Rise	115 Degrees Celsius
----------------------	---------------------