



Class 1, Div 2, Low Voltage Distribution Transformer - Single Phase, 120/208/240/277 - 120/240V, 10kVA

By Acme Electric
Catalog # [T1010K0220CSH](#)

Class 1, Div 2, Low Voltage Distribution Transformer - Single Phase, 120/208/240/277 - 120/240V, 10kVA



Features

- Class 1 Div. 2, Groups A, B, C, D
- For Hazardous Locations
- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

Specifications

Nema Rating	NEMA 3R
UL Standard	UL 506
Buy America(n) Qualified	Contact Manufacturer
UL Insulation Class	180°C

Configuration

Electrostatic Shield	Shielded
----------------------	----------

Current

Frequency Rating	60 Hz
Primary Voltage	120/208/240/277 V
kVA	10.0
Secondary Voltage	120/240 V

Dimensions

Weight	124 lb.
Height	15.19 in
Width	13.5 in
Length	10.84 in
Dimensions	10.84 in x 13.5 in x 15.19 in

General

Material type	ZFIN
Mounting Type	Wall
UPC	047503021934
Winding Material	AL
Construction	Encapsulated

Logistics

Pallet Quantity	1
Carton Quantity	1

Operational

Max Temperature Rise	115 Degrees Celsius
----------------------	---------------------