



Class 1, Div 2, Low Voltage Distribution Transformer - Single Phase, 277/480 - 208/277V, 10kVA

By Acme Electric
Catalog # [T1010K0270CSH](#)



Class 1, Div 2, Low Voltage Distribution Transformer - Single Phase, 277/480 - 208/277V, 10kVA

Features

- Class 1 Div. 2, Groups A, B, C, D
- For Hazardous Locations
- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

General

Catalog Number	T1010K0270CSH
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Secondary Voltage	208/277 V
UL Insulation Class	180°C
Winding Material	AL
kVA	10

Dimensions

Dimensions	10.84 in x 13.5 in x 15.19 in
------------	-------------------------------

Height	15.19 in
Length	10.84 in
Weight	125 lb
Width	13.5 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	277/480 V

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Nema Rating	NEMA 3R
UL Standard	UL 506

Product Assets

- [SDS - HCC SDS](#)
- [Specifications - T1010K0270CSH](#)
- [Video - Encapsulated Transformers for Hazardous Locations Class I Div 2](#)