



Class 1, Div 2, Low Voltage Distribution Transformer - Single Phase, 240X480 - 120/240V, 25kVA

By Acme Electric
Catalog # [T1025K0193CSH](#)



Class 1, Div 2, Low Voltage Distribution Transformer - Single Phase, 240X480 - 120/240V, 25kVA

Features

- Class 1 Div. 2, Groups A, B, C, D
- For Hazardous Locations
- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

General

ANFC Taps	2
BNFC Taps	4
Catalog Number	T1025K0193CSH
Construction	Encapsulated
Electrostatic Shield	Shielded
Material Type	ZFIN
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Secondary Voltage	120/240 V
Taps % Steps	2.5%
UL Insulation Class	180°C
Winding Material	AL
kVA	25

Dimensions

Dimensions	13.34 in x 16.13 in x 18.44 in
Height	18.44 in

Length	13.34 in
Weight	250 lb
Width	16.13 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	240 X 480 V

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Nema Rating	NEMA 3R
UL Standard	UL 506

Logistics

Carton Quantity	1
Pallet Quantity	1

Product Assets

[Brochures - Encapsulated Transformers for Hazardous Locations Class I, Div. 2](#)
[SDS - HCC SDS](#)
[Specifications - T1025K0193CSH](#)
[Video - Encapsulated Transformers for Hazardous Locations Class I Div 2](#)