



Class 1, Div 2, Low Voltage Distribution Transformer - Three Phase, 600? - 208Y/120V, 6kVA

By Acme Electric
Catalog # [T3006K0081CSH](#)

Class 1, Div 2, Low Voltage Distribution Transformer - Three Phase, 600? - 208Y/120V, 6kVA

Features

- Class 1 Div. 2, Groups A, B, C, D
- For Hazardous Locations
- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

General

BNFC Taps	2
Catalog Number	T3006K0081CSH
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Secondary Voltage	208Y/120 V
Taps % Steps	5.0%
UL Insulation Class	180°C
Winding Material	AL
kVA	6

Dimensions

Dimensions	8.82 in x 14.17 in x 11.83 in
------------	-------------------------------



*Representative Image

Height	11.83 in
Length	8.82 in
Weight	140 lb
Width	14.17 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	600D V

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Nema Rating	NEMA 3R
UL Standard	UL 506

Product Assets

- [Brochures - Encapsulated Transformers for Hazardous Locations Class I, Div. 2](#)
- [SDS - HCC SDS](#)
- [Specifications - T3006K0081CSH](#)
- [Video - Encapsulated Transformers for Hazardous Locations Class I Div 2](#)