



Class 1, Div 2, Low Voltage Distribution Transformer - Three Phase, 208Δ - 208Y/120V, 9kVA

By Acme Electric
Catalog # T3009K0061CSH

Class 1, Div 2, Low Voltage Distribution Transformer - Three Phase, 208Δ - 208Y/120V, 9kVA

Features

- Class 1 Div. 2, Groups A, B, C, D
- For Hazardous Locations
- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

Specifications

Nema Rating	NEMA 3R
UL Standard	UL 506
Buy America(n) Qualified	Contact Manufacturer
UL Insulation Class	180°C

Configuration

Electrostatic Shield	Shielded
----------------------	----------

Current

Frequency Rating	60 Hz
Primary Voltage	208D V
kVA	9.0
Secondary Voltage	208Y/120 V

Dimensions



Weight	180 lb.
Height	14.03 in
Width	17.77 in
Length	11.52 in
Dimensions	11.52 in x 17.77 in x 14.03 in

General

Material type	ZFIN
Taps % Steps	5.0%
Mounting Type	Wall
UPC	047503022214
Winding Material	AL
BNFC Taps	2
Construction	Encapsulated

Logistics

Pallet Quantity	1
Carton Quantity	1

Operational

Max Temperature Rise	115 Degrees Celsius
----------------------	---------------------