



Class 1, Div 2, Low Voltage Distribution Transformer - Three Phase, 480Δ - 240Δ120V, 15kVA

By Acme Electric
Catalog # [T3015K0021CSH](#)



Class 1, Div 2, Low Voltage Distribution Transformer - Three Phase, 480Δ - 240Δ120V, 15kVA

Features

- Class 1 Div. 2, Groups A, B, C, D
- For Hazardous Locations
- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

Specifications

Nema Rating	NEMA 3R
UL Standard	UL 506
Buy America(n) Qualified	Contact Manufacturer
UL Insulation Class	180°C

Configuration

Electrostatic Shield	Shielded
----------------------	----------

Current

Frequency Rating	60 Hz
Primary Voltage	480D V
kVA	15.0
Secondary Voltage	240D 120 V

Dimensions

Weight	250 lb.
Height	18.86 in
Width	20.3 in
Length	9.03 in
Dimensions	9.03 in x 20.3 in x 18.86 in

General

Material type	ZFIN
Taps % Steps	5.0%
Mounting Type	Floor
UPC	047503022283
Winding Material	AL
BNFC Taps	2
Construction	Encapsulated

Logistics

Pallet Quantity	1
Carton Quantity	1

Operational

Max Temperature Rise	115 Degrees Celsius
----------------------	---------------------