



Class 1, Div 2, Low Voltage Distribution Transformer - Three Phase, 208? - 208Y/120V, 15kVA

By Acme Electric
Catalog # [T3015K0061CSH](#)



Class 1, Div 2, Low Voltage Distribution Transformer - Three Phase, 208? - 208Y/120V, 15kVA

Features

- Class 1 Div. 2, Groups A, B, C, D
- For Hazardous Locations
- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

General

BNFC Taps	2
Catalog Number	T3015K0061CSH
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Floor
Secondary Voltage	208Y/120 V
Taps % Steps	5.0%
UL Insulation Class	180°C
Winding Material	AL
kVA	15

Dimensions

Dimensions	9.03 in x 20.3 in x 18.86 in
------------	------------------------------

Height	18.86 in
Length	9.03 in
Weight	245 lb
Width	20.3 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	208D V

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Nema Rating	NEMA 3R
UL Standard	UL 506

Product Assets

- [Brochures - Encapsulated Transformers for Hazardous Locations Class I, Div. 2](#)
- [SDS - HCC SDS](#)
- [Specifications - T3015K0061CSH](#)
- [Video - Encapsulated Transformers for Hazardous Locations Class I Div 2](#)