



Class 1, Div 2, Low Voltage Distribution Transformer - Three Phase, 480Δ - 208Y/120V, 30kVA

By Acme Electric
Catalog # T3030K0013CSH



Class 1, Div 2, Low Voltage Distribution Transformer - Three Phase, 480Δ - 208Y/120V, 30kVA

Features

- Class 1 Div. 2, Groups A, B, C, D
- For Hazardous Locations
- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

Specifications

Buy American Compliant	Contact Manufacturer
Nema Rating	NEMA 3R
UL Standard	UL 506
Buy America(n) Qualified	Contact Manufacturer
UL Insulation Class	180°C

Configuration

Electrostatic Shield	Shielded
ANFC Taps	2

Current

Frequency Rating	60 Hz
Primary Voltage	480D V
kVA	30.0
Secondary Voltage	208Y/120 V

Dimensions

Length	11.14 in
Weight	613 lb.
Height	24.81 in
Width	27.13 in
Dimensions	11.14 in x 27.13 in x 24.81 in

General

Material type	ZFIN
Taps % Steps	2.5%
Winding Material	AL
BNFC Taps	4
Mounting Type	Floor
UPC	047503001981
Construction	Encapsulated

Logistics

Pallet Quantity	1
Carton Quantity	1

Operational

Max Temperature Rise	115 Degrees Celsius
----------------------	---------------------