



Medium Voltage Transformer - Three Phase, 2400? - 208Y//120V, 1500kVA

By Acme Electric
Catalog # [WI015M10](#)



*Representative Image

Medium Voltage Transformer - Three Phase, 2400? -
208Y//120V, 1500kVA

General

Catalog Number	WI015M10
Construction	Ventilated
Mounting Type	Floor
Primary Voltage	2400Δ
Product Category	Medium Voltage Transformer
Secondary Voltage	208Y/120 V
UPC	047503099483
Winding Material	AL
kVA	1500

Dimensions

Depth	50 in
Height	90 in
Weight	7900 lb
Width	90 in

Electrical Ratings

Efficiency	99.37%
Frequency Rating	60 Hz
Primary Voltage	2400D V

Certifications And Compliance

CSA Standard	C22.2 No. 47
Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431
Nema Rating	NEMA 1
UL Standard	UL 1562

Product Assets

- [Brochures - Medium voltage dry-type transformers](#)
- [Customer Notices - Prop65_Cancer](#)
- [SDS - HCC SDS](#)
- [Specifications - WI015M10 Specification Sheet English](#)
- [Specifications - WI015M10 Specification Sheet French](#)
- [Terms and Conditions - HCC Terms & Conditions](#)