

CB Compact Balances

Convenient features for portable precision weighing



Features

- Vivid, backlit LCD easily visible in any lighting conditions
- Large, grade 304 stainless steel pan allows for swift cleaning
- Lightweight design simplifies transport and portability
- Sealed keypad protects against dirt and spills
- Level indicator and adjustable feet ensure proper balance setup for optimum weighing results
- Low-battery indicator alerts users when batteries need replacement
- Operates with AC adapter (not included) or batteries (included)
- External calibration allows for verification and adjustment with weights
- Simple operation allows quick startup and use with little or no training
- Zero-tracking feature ensures display returns to zero reading



Adjustable Feet

General Specifications

- Weighing units: g, lb, oz
- Power supply: 2 x AA Batteries, 12VDC 500mA adapter (optional)
- Display: LCD with 0.5" / 12mm-high digits
- Calibration: External
- Housing: ABS Plastic
- Operating temperature: 0° to 40°C / 32° to 104°F

Applications

- Weighing

WARRANTY
12
MONTHS

Product Details

Model	Capacity	Readability	Pan Size	Shipping Weight	Shipping Dimensions	Price
CB 501	500g	0.1g	5.1" / 130mm ø	2lb / 0.91kg	3"x9"x8" / 76x229x203mm	\$90.00
CB 1001	1000g	0.1g	5.1" / 130mm ø	2lb / 0.91kg	3"x9"x8" / 76x229x203mm	\$105.00
CB 3000	3000g	1g	5.1" / 130mm ø	2lb / 0.91kg	3"x9"x8" / 76x229x203mm	\$95.00

Accessories

Item number	Description	Price
700400123	6VDC 200mA adapter	\$30.00
700230015	In-use cover	\$15.00
700660290	Calibration certificate	\$85.00
700100378	ASTM 4 500g Calibration Weight	\$105.00
700100379	ASTM 4 1kg Calibration Weight	\$185.00
700100192	ASTM 4 2kg Calibration Weight	\$325.00