

Equinox[®] Semi-Micro and Analytical Balances

Intuitive user interface for professionals; designed for advanced applications



Semi-Micro Pan

Rear View

Features

- Large, responsive 5" 800x480 pixel touch-screen display
- Level indicator and adjustable feet ensure proper balance setup for optimum weighing results
- Security slot for optional Kensington-type lock and cable to help prevent theft
- Large, grade 304 stainless steel pan allows for swift cleaning
- RS-232 interface provides speedy connection to computers and printers
- USB host for memory card
- AC adapter included
- Built-in memory for storing products and settings
- External calibration allows for verification and adjustment with weights
- Selectable digital filtering helps minimize effects of vibration and disturbances
- Security password control prevents unauthorized access
- Printouts include date and time for data tracking within Good Laboratory Practices (GLP) guidelines
- Preset tare function speeds the process of repetitive weighing
- Parts counting with freely selectable sample sizes
- Multilingual display permits use in various regions
- Memory accumulation totals results
- Checkweighing with audible alarm

Applications

- Weighing
- Parts counting
- Percentage weighing
- Checkweighing
- Dynamic / Animal weighing
- Accumulation
- Density determination
- Peak hold
- Formulation
- Statistics
- Textile



With Density Kit

WARRANTY
36
MONTHS

General Specifications

- Weighing units: g, mg, ct, GN, lb, oz, dwt, mm, ozt, tl.H, tl.S, tl.T, T, custom unit
- Interface: RS-232, USB
- Power supply: 24VDC 1A adapter
- Display: Touchscreen with 0.5" / 13mm-high digits
- Calibration: External, Internal automatic
- Housing: ABS Plastic
- Operating temperature: 10° to 30°C / 50° to 86°F

Internal Calibration

Model	Capacity	Readability	Pan Size	Shipping Weight	Shipping Dimensions	Price
EAB 125i	62g / 120g	0.01mg/ 0.1mg	3.1" / 80mm ø	20.6lb / 9.36kg	20.9"x20.9"x15.4" / 530x530x390mm	\$4595.00
EAB 225i	82g / 220g	0.01mg/ 0.1mg	3.1" / 80mm ø	20.6lb / 9.36kg	20.9"x20.9"x15.4" / 530x530x390mm	\$5395.00
EAB 124i	120g	0.0001g	3.1" / 80mm ø	20.6lb / 9.36kg	20.9"x20.9"x15.4" / 530x530x390mm	\$2395.00
EAB 224i	220g	0.0001g	3.1" / 80mm ø	20.6lb / 9.36kg	20.9"x20.9"x15.4" / 530x530x390mm	\$2795.00
EAB 314i	310g	0.0001g	3.1" / 80mm ø	20.6lb / 9.36kg	20.9"x20.9"x15.4" / 530x530x390mm	\$3095.00
EAB 414i	410g	0.0001g	3.1" / 80mm ø	20.6lb / 9.36kg	20.9"x20.9"x15.4" / 530x530x390mm	\$3995.00
EAB 514i	510g	0.0001g	3.1" / 80mm ø	20.6lb / 9.36kg	20.9"x20.9"x15.4" / 530x530x390mm	\$4995.00

External Calibration

Model	Capacity	Readability	Pan Size	Shipping Weight	Shipping Dimensions	Price
EAB 124e	120g	0.0001g	3.1" / 80mm ø	20.6lb / 9.36kg	20.9"x20.9"x15.4" / 530x530x390mm	\$2195.00
EAB 224e	220g	0.0001g	3.1" / 80mm ø	20.6lb / 9.36kg	20.9"x20.9"x15.4" / 530x530x390mm	\$2595.00
EAB 314e	310g	0.0001g	3.1" / 80mm ø	20.6lb / 9.36kg	20.9"x20.9"x15.4" / 530x530x390mm	\$2895.00

Accessories

Item number	Description	Price	Item number	Description	Price
104008036	Anti-Vibration Table.....	\$845.00	600002028	AdamDU Data Collection Program	\$95.00
1060014262	Density kit.....	\$375.00	700660290	Calibration certificate.....	\$85.00
3012014259	In-use wet cover.....	\$35.00	700100349	ASTM 15g Calibration Weight.....	\$90.00
3014011014	RS-232 cable.....	\$35.00	700100350	ASTM 110g Calibration Weight	\$95.00
700100410	ABI-1 Ionizer.....	\$1100.00	700100351	ASTM 150g Calibration Weight	\$100.00
1120014641	AIP Impact Printer	\$335.00	700100352	ASTM 1100g Calibration Weight.....	\$105.00
1120011156	ATP Thermal Printer	\$245.00	700100188	ASTM 1200g Calibration Weight.....	\$125.00
700100046	Kensington-type lock and cable	\$28.00	700100189	ASTM 1500g Calibration Weight.....	\$135.00