



# STAINLESS STEEL Uni-Serv Speed Bars 26" Wide



Item #: \_\_\_\_\_ Qty #: \_\_\_\_\_  
 Model #: \_\_\_\_\_  
 Project #: \_\_\_\_\_



15A - 120V GFI Duplex  
 Receptacle Hidden  
 Beneath Blender Shelf 

Conforms To NSF 61/9 Lead Free Requirements

**FEATURES:**

- 30" x 15" x 12" insulated ice bin; 98 lbs. ice capacity.
- 10"W x 14"L x 7"D dump sink.
- Recessed drainboard for glassware storage.
- Dual blender/mixer recessed station with 15A - 150V GFI duplex outlet hidden beneath shelf.
- Includes two removable plastic bottle racks.
- Galvanized legs with adjustable plastic bullet feet.
- Adjustable galvanized side cross-bracing.
- 4" backsplash.
- Optional 7-circuit cold plate sealed into the bottom of the ice bin.

**Units with Cold Plates** include a soda line chase at top of splash on right & left ends of ice bin.

**MECHANICAL:**

- Includes K-52 splash mount gooseneck spout faucet.
- Faucet meet federal lead free standards.**
- 1" IPS drains (sink bowl, recessed drainboard and ice bin).
- 1/2" IPS drain (ice bin with cold plate only).
- 15 amp. - 120V duplex receptacle.

**MATERIAL:**

- 22 gauge, 300 stainless steel
- Sink Bowl:** 20 gauge, 300 stainless steel
- Understructure:** 22 gauge galvaneal front/back; 11 gauge electrogalvaneal leg channel
- Legs:** 1 5/8" O.D. 18 gauge, galvanized steel with adjustable plastic bullet feet
- Ice Bin Insulation:** 2 lbs. density styrofoam (non-cold plate models); 2 lbs. density foam-in-place (cold plate models)
- Cold Plate:** Cast aluminum with 7 circuits (5 syrup and 2 water lines) with 5/16" diameter stainless steel bump and swedge ends.

**OPTIONAL:**

- K-316-LU** - Add wrist handles
- SU-10A** - 18" stainless steel leg upgrade with cross-bracing
- SU-10C** - 14" stainless steel leg upgrade with cross-bracing

Model #	Overall Length	Ice Bin Capacity	Ice Bin Location	Approx. Weight	Approx. Cu. Ft.
CRU-60L	60"	98 lbs.	Left	110 lbs.	23
CRU-60R	60"	98 lbs.	Right	110 lbs.	23

**With 7-Circuit Cold Plate**

CRU-60L-7	60"	98 lbs.	Left	193 lbs.	23
CRU-60R-7	60"	98 lbs.	Right	193 lbs.	23

*L And R Indicate Ice Bin Location.*

 **WARNING:** Equipment that include faucets on this page may contain a chemical known to the State of California to cause cancer, birth defects or other reproductive harm.



**Customer Service Available To Assist You 1-800-645-3166 8:30 am - 8:00 pm E.S.T.**

For Orders & Customer Service:  
 Email: customer@advancetabco.com or Fax: 631-242-6900

For Smart Fabrication™ Quotes:  
 Email: smartfab@advancetabco.com or Fax: 631-586-2933

# DIMENSIONS and SPECIFICATIONS

TOL Overall: ± .500" Interior: ± .250"

ALL DIMENSIONS ARE TYPICAL

## CRU-60L-7 Series Shown (With Cold Plate)

