

Breathing Air Hose Reels



HR-100M
Manual Reel



HR-500MC
Manual Cart



HR-50
Automatic Reel

3/8" or 1/2" Breathing Air Hose Reels - Manual Rewind

Item No.	Description
HR-50M	Holds 50 feet of 3/8" ID hose or 25 feet of 1/2" ID hose
HR-100M	Holds 100 feet of 3/8" ID hose or 50 feet of 1/2" ID hose
HR-300M	Holds 300 feet of 3/8" ID hose or 150 feet of 1/2" ID hose
HR-400M	Holds 400 feet of 3/8" ID hose or 200 feet of 1/2" ID hose
HR-550M	Holds 550 feet of 3/8" ID hose or 300 feet of 1/2" ID hose
	Manual Hose Reel Cart
HR-500MC	Cart with fold down handle and roller wheels - holds 450 feet of 3/8" or 300 feet of 1/2" ID hose

**Breathing air hose must be ordered separately
See page 23.**

3/8" or 1/2" Breathing Air Hose Reels - Automatic Rewind

Item No.	Description
HR-50	Holds 50 feet of 3/8" ID breathing air hose
HR-50SS	Holds 50 feet of 3/8" ID breathing air hose, stainless steel reel
HR-100	Holds 100 feet of 3/8" ID breathing air hose
HR-100-5	Holds 100 feet of 1/2" ID breathing air hose
HR-505	Holds up to 50 feet of 1/2" ID breathing air hose
HR-575	Holds up to 75 feet of 1/2" ID breathing air hose

3/8" Automatic Rewind Reels with POA

Item No.	Description
HR-50POA	NIOSH point-of-attachment reel, holds 50' of 3/8" ID breathing air hose, installed regulator, pressure gauge, and safety relief valve. Use with NIOSH approved respirator hose.

Contact Customer Service for other lengths of hose

Reel colors may vary depending on reel type ordered.

1/4" Automatic Rewind Hose Reels - High Pressure

Item No.	Description
HPR-50	Auto hose reel, 5000 psi, holds 50 foot of 1/4" ID high pressure air hose
HPR-350	Auto hose reel, 6000 psi, holds 50 foot of 1/4" ID high pressure air hose
HPR-100	Auto hose reel, 5000 psi, holds 100 foot of 1/4" ID high pressure air hose
HPR-1006K	Auto hose reel, 6000 psi, holds 100 foot of 1/4" ID high pressure air hose

All reels can be supplied with breathing air hose installed. Hose reels can be mounted on roller carts. Consult Customer Service for additional details.