

Heavy-Duty Hazardous Location Air Circulators

Pedestal, Wall, I-Beam & Ceiling Mount Fans 115/230V or 230/460V Spark Resistant Non-Oscillating

Unit Packs 115/230 Spark Resistant Models

1 Year Warranty - Ultra Quiet

FEATURES

- Die Cast Aluminum Propeller
- OSHA Approved Safety Guards
- 115/230V, 1/4 HP, 1 Phase & 230/460V, 1/4 HP, 3 Phase, Single Speed, Ball Bearing Motors
- All Unit Packs in Stock



Prop Dia.	CFM	RPM	Motor No.	Volt	F.L. Amps
24"	5739	1140	1169	115/230	6.9/3.5
24"	5739	1140	1269	230/460	1.1/.55
30"	8723	1140	1169	115/230	6.9/3.5
30"	8723	1140	1269	230/460	1.1/.55

Performance Ratings are conducted in accordance with AMCA Standard 230-99.

Explosion Proof Motor for Class 1, Group D & Class II, Groups E, F & G See page 3 for further Explosion Proof Motor information.

FOR USE IN HAZARDOUS LOCATIONS SUCH AS:

Oil Refineries

Welding Shops

Paint Operations / Storage and Other Locations that may contain Explosive Gas, Vapor or Dust in the Atmosphere



Motor, Specified Mounting, Propeller & Guard Shipped In A Single Carton

EDP No.	Catalog No.	Prop Dia.	Fan Style	HP	Ship Wt.	List Price
20301	24LF16X	24"	Pedestal Fan	1/4	111	\$1,624
20321	24LW16X8	24"	Wall Mount	1/4	78	\$1,471
20341	24LI16X	24"	I-Beam Mount	1/4	82	\$1,547
20331	24LS16X	24"	Ceiling Mount	1/4	74	\$1,435
20351	30LF16X	30"	Pedestal Fan	1/4	98	\$1,703
20371	30LW16X8	30"	Wall Mount	1/4	82	\$1,550
20391	30LI16X	30"	I-Beam Mount	1/4	87	\$1,627
20381	30LS16X	30"	Ceiling Mount	1/4	77	\$1,513

Kitted Units 230/460 Spark Resistant Models

Unit Shipped As Individual Component Parts Via Truck Or UPS

EDP No.	Catalog No.	Prop Dia.	Fan Style	HP	Ship Wt.	List Price
20450K	24LF36X	24"	Pedestal Fan: includes 21152 (Pedestal), 21166 (Base)	1/4	100	\$1,850
20470K	24LW36X8	24"	Wall Mount Fan: includes 21187 (Tilted Wall Brkt with Safety Cable)	1/4	79	\$1,696
20490K	24LI36X	24"	I-Beam Mount Fan: includes 21191 (I-Beam Brkt, with Safety Cable)	1/4	79	\$1,776
20480K	24LS36X	24"	Ceiling Mount Fan: includes 21203 (Ceiling with Safety Cable)	1/4	69	\$1,661
20500K	30LF36X	30"	Pedestal Fan: includes 21152 (Pedestal), 21166 (Base)	1/4	107	\$1,930
20520K	30LW36X8	30"	Wall Mount Fan: includes 21187 (878W-Tilted Wall Brkt with Safety Cable)	1/4	86	\$1,777
20540K	30LI36X	30"	I-Beam Mount Fan: includes 21191 (700-U I-Beam Brkt, with Safety Cable)	1/4	86	\$1,854
20530K	30LS36X	30"	Ceiling Mount Fan: includes 21203 (Ceiling with Safety Cable)	1/4	76	\$1,741

All 24" Kitted Components consist of: 21040 (1269 XP Motor); 21070 (AC24G Guard Ass'y.); 21095 (24BA-1A Prop); plus mounting listed above.

All 30" Kitted Components consist of: 21040 (1269 XP Motor); 21080 (AC30G Guard Ass'y.); 21105 (30BA-1A Prop); and mounting listed above.

NOTES:

XP = Explosion Proof

"K" suffix indicates unit shipped as individual component parts. May be shipped UPS or Truck.

CORD AND PLUG NOT PROVIDED. Must be hard wired. Wiring must conform to all national, state and local codes.

A safety cable kit is included in all overhead mounted air circulators to prevent the fan from falling if accidentally struck or mounting fails. Single safety cable kits consist of 12 feet of 1/16" diameter cable, 2 cable clamps and instructions