



Airmaster® Fan Company

[REQUEST A CATALOG](#)

Quick Search:

EDP Number

[Search](#)

CIRCULATORS

Air Blasters
 Ceiling Fans
 Commercial Fans
 Heavy Duty Fans
 Industrial Fans
 Portable Mancoolers
 Misting Fans
 Residential/Office
 Safety Fans
 Utility Blower
 Washdown Fans

VENTILATING

Wall Fans
 Centrifugal Air Supply
 Centrifugal Exhaust
 Fans
 Centrifugal Upblast
 Fans
 Room Ventilators
 Inline Duct Fan
 Intake Louvers
 Relief Fans
 Rooftop Exhaust Fans
 Shutter Fans
 Tube Axial Fans
 Upblast Rooftop Fans
 Whole House Fans

DOCUMENTATION

Applications
 Terminology - Principles
 Warranty

LOW STAND - DIRECT DRIVE AIR BLASTERS



[Printable Page](#)
[Component Parts](#)
[Submittal Sheet](#)

FEATURES :

- LOW STAND
- CAST ALUMINUM NON-SPARKING PROPELLERS
- FRONT & REAR GUARDS MEET OSHA STANDARDS
- NON-TIPPING HEAVY BASE
- WELDED STEEL CONSTRUCTION
- PORTABLE OR STATIONARY MOUNT
- 115/230V AND 230/460/V, TOTALLY ENCLOSED AND EXPLOSION PROOF, BALL BEARING MOTORS

Prop Dia.	HP	Wt.	LOW STAND MODEL - 360° TILT			
			Totally Enclosed Motor			
			1 Phase 115/230 V		3 Phase 230/460 V	
			Cat. Number	EDP #	Cat. Number	EDP #
18"	1/4	87	18M-1/4L	22100	18MP-1/4L	22101
24"	1/4	115	24M-1/4L	22110	24MP-1/4L	22111
	1/2	120	24M-1/2L	22120	24MP-1/2L	22121
	1	130	24M-1L	22130	24MP-1L	22131
	3	160	24M-3L	22140	24MP-3L	22141
30"	1/2	141	30M-1/2L	22150	30MP-1/2L	22151
	1-1/2	200	30M-1-1/2L	22160	30MP-1-1/2L	22161
	3	220	30M-3L	22170	30MP-3L	22171
36"	1-1/2	250	36M-1-1/2L	22180	36MP-1-1/2L	22181
	2	255	36M-2L	22190	36MP-2L	22191
	3	280	-	-	36MP-3L	22401
42"	2	315	42M-2L	22210	42MP-2L	22211
	5	340	-	-	42MP-5L	22421
48"	7-1/2	685	-	-	48MP-7-1/2L	22431

NOTES: Fans are pre-assembled, tested and ready to install. Specify voltage required when ordering.

Prop Dia.	HP	Wt.	LOW STAND MODEL - 360° TILT			
			Explosion Proof Motor			
			1 Phase 115/230 V		3 Phase 230/460 V	
			Cat. Number	EDP #	Cat. Number	EDP #
18"	1/4	87	18M-1/4LX	22102	18MP-1/4LX	22103
24"	1/4	115	24M-1/4LX	22112	24MP-1/4LX	22113
	1/2	120	24M-1/2LX	22122	24MP-1/2LX	22123
	1	130	24M-1LX	22132	24MP-1LX	22133
	3	160	-	-	24MP-3LX	22143
30"	1/2	141	30M-1/2LX	22152	30MP-1/2LX	22153
	1-1/2	200	30M-1-1/2LX	22162	30MP-1-1/2LX	22163
	3	220	-	-	30MP-3LX	22173
36"	1-1/2	250	36M-1-1/2LX	22182	36MP-1-1/2LX	22183
	2	255	36M-2LX	22192	36MP-2LX	22193
	3	280	-	-	36MP-3LX	22409
42"	2	315	-	-	42MP-2LX	22213
	5	340	-	-	42MP-5LX	22423
48"	7-1/2	385	-	-	48MP-7-1/2LX	22433

NOTES: Fans are pre-assembled, tested and ready to install. Specify voltage required when ordering.

© 2008 Airmaster Fan Company

Designed & Powered By: **Digital Dynamic Productions**