

Portable Mancoolers® - 115V

EMC Belt Drive Models



2 Year Warranty - Engineered for Superior Performance
FEATURES ON ALL BELT DRIVE MANCOOLERS®

- Guards Epoxy Coated
- Barrel Epoxy Coated

BDMC36C

- 115V, 1 Phase, 2 Speed, ODP, 1/2 HP Motor
- 36" Diameter Three Bladed Aluminum Propeller
- Tilttable
- Two Speed Rocker Switch
- Steel Wheels with Rubber Tires
- Handle with Cord Wrap
- 10' Cord with Three Prong Plug



EDP No.	Catalog No.	Prop Dia.	Fan Style	HP	Cabinet Size	CFM	RPM	Ship Wt.	List Price
70005	BDMC36C	36"	Portable	1/2 (2 Speed)	36½"	7800/5300	660/450	116	\$720



2 Year Warranty

EMC48B

- 115V, 1 Phase, 1 Speed, ODP, 1 HP Motor
- Four Bladed Epoxy Coated Steel Propeller
- Steel Wheels with Rubber Tires
- Front Leg Bracket, Pull Handle
- 12' Three Conductor SJT Type Cord and Switch



EDP No.	Catalog No.	Prop Dia.	Fan Style	HP	Cabinet Size	CFM	RPM	Ship Wt.	List Price
60019	EMC48B	48"	Portable	1 (1SP)	48½"	17,173	385	165	\$ 1,740

Belt Drive Portable Mancoolers®

1 Year Warranty

FEATURES

- 115V, 1/2 HP (36") or 1 HP (42"), 1 Phase, 2 Speed, ODP, Ball Bearing Motor
- Aluminum Four Bladed Propeller
- Epoxy Coated Steel Guards and Housing
- 8" Steel Wheels
- Full Width Easy Grip Handle
- 550 Watts (36"), 630 Watts (42")
- Grounded Plug and 10' Cord
- 2 Speed Rocker Switch
- Velocity: 159 fpm @ 90 feet
- Fully Assembled



PERFORMANCE 115V

Prop Dia.	CFM		RPM		dBA	
	High	Low	High	Low	High	Low
36"	8758	7962	600	545	68	65
42"	13036	11850	582	517	70	66



EDP No.	Catalog No.	Prop Dia.	Fan Style	HP	Ship Wt.	List Price
78938	LC36BD	36"	Portable	1/2	82	\$579
78933	LC42BD	42"	Portable	1	103	\$704