

**Pedestal & Wall/Ceiling Mounts
Non-Oscillating Models - Unit Packs**

2 Year Warranty

FEATURES

- Models are UPS Shippable in One Carton
- Pedestal Models Adjust 43" - 63"; 26" Base Diameter
- Wall/Ceiling Mount Models Include Safety Cable
- All Stocked
- 115V, 1/4 HP Non-Oscillating, 1 Phase, 3 Speed, Totally Enclosed Air Over Ball Bearing Motor
- Galvanized Steel Propeller
- 15' Supply Cord and Three Prong Plug Included

PERFORMANCE 115V

Prop Dia.	CFM			RPM			F.L. Amps
	High	Med.	Low	High	Med.	Low	
24"	4400	3460	2460	1100	800	600	3.5
30"	6100	4400	2700	1100	800	600	3.5



Adjustable Floor Model
Solid Base



Non-Oscillating
Ceiling Mount



Non-Oscillating
Wall Mount



EDP No.	Catalog No.	Prop Dia.	Fan Style	HP	Ship Wt.	List Price
71584	CA24APE	24"	Adjustable Floor (S.B.)	1/4	82	\$514
71572	CA24WC	24"	Wall/Ceiling Mount	1/4	42	\$403
71586	CA30APE	30"	Adjustable Floor (S.B.)	1/4	87	\$528
71573	CA30WC	30"	Wall/Ceiling Mount	1/4	49	\$726

Unit Pack - Motor specified Style Mounting, Propeller & Guard shipped in a single carton.

MOTOR TILT ADJUSTMENTS

TYPE	TILT UP OR DOWN (IN DEGREES)	
	NON-OSCILLATING	
	UP	DOWN
FLOOR	30°	15°
WALL	30°	50°
I-BEAM	30°	15°
CEILING	0°	90°

0° = Horizontal Plane

A safety cable kit is included in all overhead mounted air circulators to prevent the fan from falling if accidentally struck or mounting fails. Single safety cable kits consist of 12 feet of 1/16" diameter cable, 2 cable clamps and instructions.

Non-Oscillating Head Assemblies

PERFORMANCE 115V

Prop Dia.	CFM			RPM			F.L. Amps
	High	Med.	Low	High	Med.	Low	
18"	2520	---	1850	1480	---	1020	2.6
20"	2670	---	2035	1615	---	1240	2.6
24"	4400	3460	2460	1100	800	600	3.5
30"	6100	4400	2700	1100	800	600	3.5



Non-Oscillating
Head Assembly

EDP No.	Catalog No.	Prop Dia.	Fan Style	HP	Ship Wt.	List Price
37113	I-18TEHA	18"	Head Assembly	1/15*	24	\$325
37114	I-20TEHA	20"	Head Assembly	1/15*	25	\$339
71590	CA24	24"	Head Assembly	1/4	39	\$376
71591	CA30	30"	Head Assembly	1/4	48	\$388

Motor, Guard and Propeller Pre-assembled.

* Motor is 2 speed.

**30" Head Assembly is UPS OverSize 2.

FOR 18" or 20" FLOOR / COUNTER MODEL FANS – SELECT ASSEMBLED HEAD; PEDESTAL - 73103 (PAGE 17); AND BASE - 21153 (PAGE 17)