



Airmaster® FAN

INDUSTRIAL AIR CIRCULATORS

- 115V, 1 phase, 3 speed, 1/3 HP, totally enclosed air over motors
- Adjustable pedestal
- Wall/Ceiling Mount includes safety cable
- 15' supply cord and three prong plug included
- Packaged in one UPS shippable carton
- 3 year warranty

PERFORMANCE - 115V

Prop Dia.	CFM			RPM			HP	F.L. Amps
	High	Med	Low	High	Med	Low		
Non-Oscillating								
24"	5220	4020	2820	1080	700	540	1/3	3.0
30"	7185	5300	3415	1080	700	540	1/3	3.0
Oscillating								
24"	5548	4699	4062	1110	958	856	1/3	3.2
30"	7794	5943	5143	1091	871	759	1/3	3.2



Non-Oscillating
Ceiling Mount



Non-Oscillating
Wall Mount

Oscillating
Wall Mount

Non-oscillating & Oscillating
Adjustable Pedestal

NON-OSCILLATING MODELS

UNIT PACKS - Motor, Mounting, Propeller & Guard in Single Carton

Prop Dia.	Fan Style	EDP No.	Catalog No.	Ship Wt.
24"	Wall/Ceiling Mount	71725	I-24W2A	44
24"	Adjustable Pedestal	71760	UPI-24PA2A	81
30"	Wall/Ceiling Mount	71726	I-30W2A	49
30"	Adjustable Pedestal	71526	UPI-30PA2A	90

OSCILLATING MODELS

UNIT PACKS - Motor, Mounting, Propeller & Guard in Single Carton

Prop Dia.	Fan Style	EDP No.	Catalog No.	Ship Wt.
24"	Wall Mount	71565	I-24-OIW	57
24"	Adjustable Pedestal	71567	I-24-OAP	86
30"	Wall Mount	71566	I-30-OIW	61
30"	Adjustable Pedestal	71568	I-30-OAP	95

1300 Falahee Road
Jackson, MI 49203

517.764.2300

517.764.3838 F

www.airmasterfan.com