

# Akro-Tilt Trucks

- Trucks nest for shipping, saving on freight and space
- Wheel base and heavy-duty caster combination provides easy maneuverability even with heavy loads
- Models with forklift channels allow fully loaded Akro-Tilt Trucks to be moved and maneuvered by lift trucks, saving time, money and effort†
- Powder-coated tubular frame, constructed of 1.05" O.D. x 13-gauge and 1.3125" O.D. x 13-gauge wall tubes, extends under top rim for added strength
- Fully welded, reinforced frame is optimized for automatic dumper applications



77710F



Optional forklift channels allow loaded trucks to be easily lifted and moved



Akro-Tilts have 13-gauge metal lift handles which work with tilt cart dumpers



77405GREY



77410GREY



77505GREY



77510GREY



77610GREY



77710GREY



77810GREY

| Akro-Tilt Trucks |                               |                      | Dimensions (In.) |    |    | Wheels         |             | Capacity |          |         |             |
|------------------|-------------------------------|----------------------|------------------|----|----|----------------|-------------|----------|----------|---------|-------------|
| Model No.        | Model No. with Fork Channels† | Description          | W                | D  | H  | Wheel Diameter | Wheel Type* | Gal.     | Cu. Yds. | Cu. Ft. | Load Rating |
| 77405GREY        | 77405FGREY                    | Medium-Duty 100      | 29               | 59 | 38 | 12             | SP          | 100      | 1/2      | 13.5    | 600 lbs.    |
| 77410GREY        | 77410FGREY                    | Medium-Duty 200      | 33               | 68 | 42 | 12             | SP          | 200      | 1        | 27      | 600 lbs.    |
| 77505GREY        | 77505FGREY                    | Heavy-Duty 100       | 29               | 59 | 38 | 10             | MR          | 100      | 1/2      | 13.5    | 1000 lbs.   |
| 77510GREY        | 77510FGREY                    | Heavy-Duty 200       | 33               | 68 | 42 | 10             | MR          | 200      | 1        | 27      | 1000 lbs.   |
| 77610GREY        | 77610FGREY                    | Super-Heavy-Duty 200 | 33               | 68 | 42 | 12             | MR          | 200      | 1        | 27      | 2000 lbs.   |
| 77710GREY        | 77710FGREY                    | Heavy-Duty 300       | 38               | 85 | 50 | 12             | MR          | 300      | 1-1/2    | 40.5    | 2000 lbs.   |
| 77810GREY        | 77810FGREY                    | Heavy-Duty 400       | 48               | 86 | 50 | 12             | MR          | 400      | 2        | 54      | 2000 lbs.   |

\*SP = Semi-Pneumatic MR = Mold-On Rubber †Forklift channel option eliminates nestability of units.