

AX Welded Master Links



Part #	Trade Size	WLL 4:1 (lbs)*	WLL 5:1 (lbs)**	Weight (lbs)	Inside Dimensions (in)			Chain Size	
					i-length	i-width	dia	1 leg	2 leg
AX13	1/2	6,000	4,800	0.75	4.33	2.36	0.51	7/32", 9/32", 5/16"	7/32"
AX16W	5/8	8,600	7,000	1.47	5.51	3.15	0.63	5/16"	9/32"
AX18W	3/4	12,900	11,400	2.02	5.91	3.54	0.71	3/8"	5/16"
AX22	7/8	17,600	17,200	3.30	6.30	3.54	0.87	1/2"	3/8"
AX26	1	30,000	29,900	5.06	7.09	3.94	1.02	5/8"	1/2"
AX32	1-1/4	39,100	35,200	8.58	7.87	4.33	1.26	3/4"	5/8"
AX36	1-1/2	61,100	48,800	13.97	10.24	5.51	1.42	7/8"	3/4"
AX45	1-3/4	74,000	70,400	28.16	13.39	7.09	1.77	1"	7/8"
AX51	2	103,400	102,600	37.84	13.78	7.48	2.01	1-1/4"	1"
AX57	2-1/4	178,900	143,120	53.24	15.75	7.87	2.24	-----	1-1/4"

*For use with chain slings **For use with wire rope and synthetic slings

AKX Welded Master Link Assemblies



Part #	Trade Size	WLL 4:1 (lbs)*	WLL 5:1 (lbs)**	Weight (lbs)	Inside Dim. Masters (In)			Inside Dim. Subs (In)			For Chain
					i-length	i-width	dia	i-length	i-width	dia	
AKX1813W	3/4	11,200	11,000	2.90	5.91	3.54	0.71	2.13	0.98	0.51	7/32"+9/32"
AKX2216	7/8	15,200	12,200	4.88	6.30	3.54	0.87	2.76	1.34	0.63	9/32"+5/16"
AKX2618	1	26,000	21,300	7.39	7.09	3.94	1.02	3.35	1.57	0.71	3/8"
AKX3222	1-1/4	39,000	35,200	13.24	7.87	4.33	1.26	4.53	1.97	0.87	1/2"
AKX3626	1-1/2	58,700	57,200	21.98	10.24	5.51	1.42	5.51	2.56	1.02	5/8"
AKX5132	2	91,700	77,000	51.26	13.78	7.48	2.01	5.91	2.76	1.26	3/4"
AKX5136	2	110,900	88,720	56.76	13.78	7.48	2.01	6.69	2.95	1.42	7/8"
AKX5740	2-1/4	155,100	124,080	77.44	15.75	7.87	2.24	6.69	3.15	1.57	1
AKX7150	2-3/4	235,000	188,000	149.60	18.11	9.84	2.76	7.87	3.93	1.97	1-1/4"

*For use with chain slings **For use with wire rope and synthetic slings

AWX Welded Master Link Assemblies with Extra Large Sub-Links



Part #	Trade Size	WLL 4:1 (lbs)*	WLL 5:1 (lbs)**	Weight (lbs)	Inside Dim. Masters (In)			Inside Dim. Subs (In)			For Chain
					i-length	i-width	dia	i-length	i-width	dia	
AWX1813	3/4	11,200	11,000	3.52	5.91	3.54	0.71	4.33	2.36	0.51	7/32"+9/32"
AWX2216	7/8	15,200	12,200	5.63	6.30	3.54	0.87	4.33	2.36	0.63	9/32"+5/16"
AWX2618	1	26,000	21,300	8.58	7.09	3.94	1.02	5.31	2.95	0.71	3/8"
AWX3222	1-1/4	39,000	35,200	15.18	7.87	4.33	1.26	6.30	3.55	0.87	1/2"
AWX3626	1-1/2	58,700	57,200	24.09	10.24	5.51	1.42	7.09	3.94	1.02	5/8"

*For use with chain slings **For use with wire rope and synthetic slings

AWXO Welded Master Link Assemblies for Large Crane Hooks with Large Sub-Links



Part #	For Chain Size	WLL 4:1 (lbs)*	WLL 5:1 (lbs)**	Weight (lbs)	Inside Dim. Masters (in)			Inside Dim. Subs (in)		
					i-length	i-width	dia	i-length	i-width	dia
AWXO3016	9/32-5/16	14,800	11,840	14.37	13.40	7.10	1.18	4.33	2.36	0.63
AWXO3018	3/8	22,900	18,320	15.55			1.18	5.31	2.95	0.71
AWXO4022	1/2	39,000	31,200	28.60			1.57	6.30	3.54	0.87
AWXO4026	5/8	58,700	46,960	32.10			1.57	7.09	3.94	1.02

*For use with chain slings **For use with wire rope and synthetic slings