

MA SERIES SPECIFICATIONS and DIMENSIONS (inches and pounds unless noted)

Base Model	Working Load Limit (WLL)	Fall	Chain (mm)	A" Min.	B"	C"	D"	E"	P (lbs) Max.	W (lbs) /Ft. lift	W ⁽¹⁾ (lbs) 10 Lift
MA005	1/2t (1100 lbs)	1	5 x 15	13.8	5.4	0.95	0.84	5.7	56	0.74	20
MA010	1t (2200 lbs)	1	6 x 18	15.1	6.1	1.13	1.04	6.3	64	0.92	26
MA015	1.5t (3300 lbs)	1	7 x 21	17.4	6.9	1.30	1.15	7.2	69	1.12	36
MA020	2t (4400 lbs)	1	8 x 24	19.1	7.0	1.46	1.35	8	77	1.30	44
MA030	3t (6600 lbs)	1	10 x 28	21.8	8.1	1.65	1.41	10	84	1.88	72
MA040	4t (8800 lbs)	2	9 x 27	27.1	7.4	1.81	1.74	9.8	67	2.88	93
MA050	5t (11000 lbs)	2	9 x 27	27.1	7.4	1.81	1.74	9.8	84	2.88	93
MA060	6t (13200 lbs)	3	9 x 27	27.2	7.4	1.81	1.74	16.9	66	4.13	136
MA075	7.5t (16500 lbs)	3	9 x 27	27.2	7.4	2.06	2.24	16.9	83	4.13	136
MA080	8T (16000 lbs)	3	9 x 27	27.2	7.4	2.06	2.24	16.9	80	4.13	136
MA100	10t (22000 lbs)	4	9 x 27	30.1	7.4	2.06	2.24	18.1	86	5.38	165
MA120	12t (26400 lbs)	6	9 x 27	35.4	7.9	3.21	2.66	28.3	2 x 68	8.26	332
MA150	15t (33000 lbs)	6	9 x 27	35.4	7.9	3.21	2.66	28.3	2 x 85	8.26	332
MA200	20t (44000 lbs)	8	9 x 27	37.4	7.9	3.21	2.66	33.5	2 x 86	10.76	422
MA250	25t (55000 lbs)	10	9 x 27	45.3	14.5	3.21	2.66	27.5	2 x 89	13.26	509
MA300	30t (66000 lbs)	10	10 x 28	45.3	15.3	3.21	2.66	29.5	2 x 87	15.76	546

(1) Shipping weight can be estimated by adding approx. 25% to "W" hanging weight.


Standard lift = 10, 15 and 20 Ft. hand chain drop is 2 Ft less than lift. Custom lifts are available.

Option: V = Overload Protection, new design one-way operation that will lower any load. **ONE WAY**

U = USA made load chain including USA load test (except 1/2t).

How to Order, by descriptive model number

Example: Model **MA050-20-18VU**



Before using these products; Read and follow instructions in the operator's manual. Never exceed capacity. Do not use for lifting people or loads over people

