



Web Slings | Eye & Eye and Endless Slings

FEATURES

- ▶ Heavy Duty Polyester Web Slings available in 1 or 2 ply. Lengths are measured from bearing point to bearing point.
- ▶ Eyes are reinforced with polyester wear pads. Working load limits are rated at a 5:1 design factor.

Eye & Eye Sling

1-Ply Heavy Duty (Class 7)



Part #	Sling Width	Eye	Work Load Limit (lbs)			Base Length	Weight	Add
	(in)	Length (in)	Vertical	Choker	Basket	(ft)	(lbs)	Weight/ft
EE 1901	1	10	1,600	1,280	3,200	3	0.40	0.06
EE 1902	2	12	3,200	2,500	6,400	3	0.80	0.12
EE 1903	3	12	4,800	3,840	9,600	3	1.40	0.18
EE 1904	4	12	6,400	5,000	12,800	3	1.90	0.24

Note: 1" & 2" slings have flat eyes. 3" & 4" slings have tapered eyes (folded in half)

2-Ply Heavy Duty (Class 7)

Part #	Sling Width	Eye	Work Load Limit (lbs)			Base Length	Weight	Add
	(in)	Length (in)	Vertical	Choker	Basket	(ft)	(lbs)	Weight/ft
EE 2901	1	10	3,200	2,500	6,400	3	0.50	0.13
EE 2902	2	12	6,400	5,000	12,800	3	0.90	0.25
EE 2903	3	12	8,800	7,040	17,600	3	1.70	0.38
EE 2904	4	12	12,000	9,600	24,000	3	2.30	0.50

Note: 1" & 2" slings have flat eyes. 3" & 4" slings have tapered eyes (folded in half)

Endless Web Sling

1-Ply Heavy Duty (Class 7)



Part #	Sling Width	Work Load Limit (lbs)			Base Length	Weight	Add
	(in)	Vertical	Choker	Basket	(ft)	(lbs)	Weight/ft
EN 1901	1	3,200	2,560	6,400	3	0.40	0.12
EN 1902	2	6,400	5,000	12,800	3	0.80	0.24
EN 1903	3	9,400	7,520	18,800	3	1.30	0.36
EN 1904	4	12,400	9,920	24,800	3	1.70	0.48

2-Ply Heavy Duty (Class 7)

Part #	Sling Width	Work Load Limit (lbs)			Base Length	Weight	Add
	(in)	Vertical	Choker	Basket	(ft)	(lbs)	Weight/ft
EN 2901	1	6,400	5,000	12,800	3	0.80	0.25
EN 2902	2	12,400	9,920	24,800	3	1.60	0.50
EN 2903	3	17,600	14,080	35,200	3	2.60	0.76
EN 2904	4	22,000	17,600	44,000	3	3.40	1.00

Wear Pads

High Density Felt Wear Pads. 5/16" Thick



Part #	Sleeve Width (in)	Sleeve Length (in)	For Round Slings	For Web Slings
WP4X12	4	12	DR1, DR2, DR3	EE & EN 1" & 2"
WP6X12	6	12	DR4, DR5, DR6, DR7	EE & EN 3" & 4"
WP4X36	4	36	DR1, DR2, DR3	EE & EN 1" & 2"
WP6X36	6	36	DR4, DR5, DR6, DR7	EE & EN 3" & 4"