

Netway[®] FIBER SOLUTIONS

SPECTRUM

Ethernet over Fiber Hardened PoE+ Switch

Features:

- UL Listed in the U.S. and Canada for Information Technology Equipment, CE Approved.
- One (1) Gigabit SFP port (uplink).
- Two (2) ports up to 60W and 1 port up to 30W (10/100/1000 each).
- Supports PoE (802.3af), PoE+ (802.3at) and Hi-PoE devices.
- Input: 48-56VDC.
- Control, monitor and report power/diagnostics from anywhere over the network.

NETWAYSP3B



Embedded
LiNQ
TECHNOLOGY

Units with Power Supply/Charger:

- 115VAC/230VAC input.
- 120W max output.
- Built-in battery charger.
- Integral surge protection.



152

NetWay Spectrum Model #	Configuration	Dimensions
NetWaySP3B	3-port switch board only	5.6"L x 4.5"W x 0.625"H
NetWaySP3PL	3-port PoE+ Hardened Switch on Backplane	10.75"H x 8.875"W x 2.375"D
NetWaySP3WPN	Outdoor 3-port Hardened Switch only in NEMA4/4X, IP66-11 enclosure	13.31"H x 11.31"W x 5.59"D
NetWaySP3WPP	Outdoor 3-port PoE+ Hardened Switch in NEMA4/4X, IP66-11 enclosure	13.31"H x 11.31"W x 5.59"D
NetWaySP3WPPX	Outdoor 3-port PoE+ Hardened Switch in larger NEMA4/4X, IP66-11 enclosure, which accommodates four (4) 12VDC/4AH batteries (48V of backup).	17.53"H x 15.3"W x 6.67"D
NetWaySP3X	Indoor 3-port PoE+ Hardened Switch	13.5"H x 13"W x 3.25"D