

AC HYDRAULIC TRANSMISSION JACKS



AME International presents AC Hydraulic A/S Transmission Jacks, pedal operated and perfect for those who need both hands free for work. Each jack allows precise adjustment and positioning.



All jacks come with some form of safety feature such as a hand operated dead man's release and/or a built-in safety overload valve for optimum safety while in use. Models VL6 / VL10 / VLT12 are manufactured with a galvanized support saddle and base frame during lifting and lowering. Mining jack handle length: 51.2" (130 cm).



Model	Capacity	Stroke	Min. Height	Max. Height	Width	Wheel Diameter	Air Supply	Weight
VL6	0.65 tons	-	44.49" (11.3 cm)	77.36" (196.5 cm)	20.87" (53 cm)	3.15" (8 cm)	-	73 lbs (33 kg)
VL10	1.1 tons	-	46.06" (117 cm)	78.74" (200 cm)	21.65" (55 cm)	4.92" (12.5 cm)	-	88 lbs (40 kg)
VLT6	0.65 tons	47.05" (119.5)	28.35" (72 cm)	75.39" (191.5 cm)	37.4" (95 cm)	4.92" (12.5 cm)	8.5-12 bar	111 lbs (53 kg)
VLT12	1.3 tons	-	35.63" (90.5 cm)	75.59" (192 cm)	28.35" (72 cm)	4.92" (12.5 cm)	-	150 lbs (70 kg)

WJN5 WJN10 HYDRAULIC WORKSHOP CRANES

- Hydraulic workshop crane for auto workshops and service vans
- Foldable within seconds for quick and easy storage
- When folded the crane takes up a minimum of space on the workshop floor
- Jib arm with large lifting capacity – even in 5th position
- Hard chromium plated piston rod and pump piston for long life
- Built-in safety overload valve
- Fitted with 2 castors and 2 fixed wheels for easy maneuverability even with maximum load
- Lifting hook pivots 360°
- Hand operated dead man's release for optimum safety while lowering



FOLDS WITHIN SECONDS FOR EASY STORAGE

AUTO

Model	Capacity	Lifting Height	Jib Arm	Dimensions (L x W x H)	Inner Width	Weight
WJN5	0.6 tons	79.53" - 92.13" (202 - 234 cm)	37.6" - 54.13" (95.5 - 137.5 cm)	55.21" (142 cm) x 42.52" (108 cm) x 59.84" (152 cm)	37.6" (95.5 cm)	165 lbs (75 kg)
WJN10	1.2 tons	79.53" - 92.13" (202 - 234 cm)	37.6" - 54.13" (95.5 - 137.5 cm)	55.21" (142 cm) x 43.7" (111 cm) x 59.84" (152 cm)	38.78" (98.5 cm)	200 lbs (95 kg)