

Solid Steel Rectangular Padlocks

Solid steel locks have a zinc chromate finish. Available with chains (W) attached to the shackle. **Stainless steel shackles available (SS)**

Shrouded Padlocks

Shackle shrouds offer the greatest protection against cutting and prying attacks.

For A5200GLN Series: body width=1-3/4" (44mm), body thickness=3/4" (19mm), shackle diameter=5/16" (8mm), and horizontal clearance=3/4" (19mm)

Specifications	Models		
5-pin	A5200GLN A5200GLSHN A5200GLWN	A5201GLN A5201GLWN	A5202GLN A5202GLWN
Shackle Height	1-1/8" (28mm)	2" (50mm)	3" (75mm)

Keying Options – Keyed Alike (KA), Keyed Different (KD), Master Keyed (MK)



Solid Brass Rectangular Padlocks

Solid brass locks are available in two body widths with choice of hardened steel or brass shackle.

For A5560NB Series: body width=1-3/4" (44mm), body thickness=3/4" (19mm), shackle diameter=5/16" (8mm), and horizontal clearance=3/4" (19mm)

For ASL40N Series: body width=1-1/2" (38mm), body thickness=3/4" (19mm), shackle diameter=1/4" (6mm), and horizontal clearance=3/4" (19mm)

Specifications	Models		
5-pin	ASL40N		ASL42N
5-pin		A5560N	
Shackle Height	1" (25mm)	1-1/8" (28mm)	3" (75mm)

Keying Options – Keyed Alike (KA), Keyed Different (KD), Master Keyed (MK)

