

# Industrial Applications

## Gloves, Natural Rubber Latex

With great flexibility and good resistance to many acids and alcohols, Ansell's Natural Rubber Latex gloves make a comfortable choice for chemical and liquid protection. Compare gloves using this information to determine which rubber latex glove works best for you.



### A. AciTek™ 49-252 NEW

- Cleanroom certified protection against acids, etchants and solvents.
- Unlined, straight cuff, fishscale finish, 20 mil thickness, 14" length
  - Suitable for Class 100 (ISO 5) / Grade A Clean Room environments
  - Compliant with ASTM and IEST standards
  - Manufactured in a facility certified to ISO 9001 standards



### B. Marigold® Astroflex

- Flexibility and high dexterity and a seamless nylon liner.
- Nylon liner, gauntlet cuff, rough crinkle finish, 50 mil thickness, 12" length
  - Anatomical shape with curved fingers
  - Provides thermal insulation up to 482°F (250°C) or down to 482°F (-20°C) conditions
  - Food handling 21 CFR 177.2600 compliant



### C. Marigold® Emperor Medium Weight ME104

- Superior chemical protection glove is chlorinated to harden and cleanse glove surface.
- Unlined, beaded cuff, smooth finish, 47 mil thickness, 17" length
  - Ideal for use when heavy duty protection is essential



### D. Marigold® Emperor Heavy Weight ME105 E. ME108

- Superior chemical protection glove is chlorinated to harden and cleanse glove surface.
- Unlined, beaded cuff, smooth finish, 59 mil thickness
  - Ideal for use when heavy duty protection is essential
  - **ME105:** 17" length
  - **ME108:** 24" length

NOTE: ANSI/ISEA 2016 Cut ratings estimated based on pending test results

Key	Description	Style No.	ANSI/ ISEA 2016 Cut Rating	ANSI/ ISEA Abrasion Level	Color	Grip Pattern	Liner Material	Cuff Style	Palm Thickness	Glove Length	FDA Food Contact	Sizes
A.	AciTek™	49-252	A0	2	Citrus Orange	Fishscale	Unlined	Straight	20 mil	14"		XS (7), S (8), M (9), L (10)
B.	Marigold®	Astroflex	A0	3	Blue	Crinkle	Polyamide	Gauntlet	50 mil	12"		XXS (6), XS (7), S (8), M (9), L (10), XL (11)
C.	Marigold® Emperor Mediumweight	ME104	A0	3	Black	Smooth	Unlined	Beaded	47 mil	17"		7.5, 8.5, 9.5, 10.5*
D.	Marigold® Emperor Heavyweight™	ME105	A0	3	Black	Smooth	Unlined	Beaded	59 mil	17"		7.5, 8.5, 9.5, 10.5*
E.	Marigold® Emperor Heavyweight™	ME108	A0	3	Black	Smooth	Unlined	Beaded	59 mil	24"		7.5, 8.5, 9.5, 10.5*

\*Available ONLY in half sizes