

Industrial Applications

Gloves, Natural Rubber Latex

With great flexibility and good resistance to many acids and alcohols, Ansell's Natural Rubber Latex gloves make a comfortable choice for chemical and liquid protection. Compare gloves using this information to determine which rubber latex glove works best for you.



A. Marigold® G31H Featherweight Plus

Medium-weight glove offers moderate chemical protection.

- Unlined, beaded cuff, raised diamond finish, 15 mil thickness, 13" length
- Excellent dexterity, tensile strength and elasticity
- Food handling 21 CFR 177.2600 compliant



B. Marigold® Tripletec Plus™ G43Y

Durable glove coated with an extra layer of Nitrile for longer life.

- Cotton flock lined, beaded cuff, raised diamond finish, 20 mil thickness, 13" length
- Triple dip glove coated with Nitrile for longer life
- Resistance to oils, fats, chemicals and detergents

Did You Know?

Research indicates that around 8 in 10 chemical glove wearers have problems with hand sweat, poor grip, and poor fit when wearing chemical gloves.

Source: Ansell Market Research 2015

NOTE: ANSI/ISEA 2016 Cut ratings estimated based on pending test results

Key	Description	Style No.	ANSI/ ISEA 2016 Cut Rating	ANSI/ ISEA Abrasion Level	Color	Grip Pattern	Liner Material	Cuff Style	Palm Thickness	Glove Length	FDA Food Contact	Sizes
A.	Marigold® Featherweight Plus	G31H	A0	3	Natural	Raised Diamond	Unlined	Beaded	15 mil	13"		6.5, 7.5, 8.5, 9.5*
B.	Marigold® Tripletec Plus™	G43Y	A0	3	Yellow	Raised Diamond	Flock Lined	Beaded	20 mil	13"		6.5, 7.5, 8.5, 9.5*

*Available ONLY in half sizes