

AS 611 EG, GR, ZTC

"Z" SUPPORT

Use with AS 200, AS 210, & AS 500 BTB
Std Pkg 50 - Wt./100 pcs: 54 Lbs.

AS 609 EG, GR

2-HOLE OFFSET "Z" SUPPORT

Std Pkg 25 - Wt./100 pcs: 38 Lbs.

AS 756 EG, GR, ZTC

"Z" SUPPORT

Use with AS 100, AS 200 BTB, & AS 210 BTB
Std Pkg 25 - Wt./100 pcs: 70 Lbs.

AS 3060 EG, GR

OFFSET CONNECTOR

A	Wt./100 Pcs.
4"	77
5"	95
6"	98
7"	105
8"	120

Std Pkg 25 - Wt./100 pcs: See chart above.

"Z" SUPPORT

<input type="checkbox"/> AS 612	<input type="checkbox"/> EG, <input type="checkbox"/> GR
<input type="checkbox"/> AS 711	<input type="checkbox"/> EG, <input type="checkbox"/> GR
<input type="checkbox"/> AS 928	<input type="checkbox"/> EG, <input type="checkbox"/> GR, <input type="checkbox"/> ZTC
<input type="checkbox"/> AS 2601	<input type="checkbox"/> EG, <input type="checkbox"/> GR

Std Pkg & Wt./100 pcs: See chart above.

Catalog No.	A	Std. Pkg.	Wt./100 Pcs.	Use With
AS 612	1"	50	50	AS 400
AS 2601	2 ⁷ / ₁₆ "	25	66	AS 150
AS 711	1 ³ / ₈ "	25	53	AS 300
AS 928	1 ³ / ₁₆ "	50	47	AS 500 & AS 520

Page notes unless otherwise specified: 1/4" thick, 1 5/8" wide, holes 9/16" diameter, spaced 1 7/8" on center and 1 3/16" from end.

LEGEND:

GR: Powder Coated Supr-Green EG: Electro-Galvanized PG: Pre-Galvanized AL: Aluminum HG: Hot Dipped Galvanized PL: Plain SS: Stainless Steel ZTC: Zinc Trivalent Chromium
Stainless Steel (SS), Zinc Trivalent Chromium (ZTC) and Hot Dipped Galvanized (HG) are specialty finishes. Pricing is located in the Specialty Strut Section of the Anvil-Strut price book.

PROJECT INFORMATION		APPROVAL STAMP	
Project:		<input type="checkbox"/> Approved	
Address:		<input type="checkbox"/> Approved as noted	
Contractor:		<input type="checkbox"/> Not approved	
Engineer:		Remarks:	
Submittal Date:			
Notes 1:			
Notes 2:			