

Fig. 80-V and 81-H

Weight Chart (approx) lbs, each

Hanger Sizes	Fig 80-V			Fig 81-H			
	Types A, B, C, D & E		Type G ■	Types A, B, C, D & E		Type F	
	Net	Shipping	Net	Net	Shipping	Net	Shipping
1 to 3	–	–	–	18	20	–	–
4 to 6	–	–	–	21	23	–	–
7 to 9	–	–	–	23	25	–	–
10 to 12	62	67	160	52	57	174	179
13 to 15	65	70	166	55	60	177	182
16 to 18	70	75	176	60	65	182	187
19 to 20	163	171	371	150	158	415	423
21 to 23	165	173	375	152	160	417	425
24 to 26	172	180	389	159	167	424	432
27 to 29	180	188	405	167	175	432	440
30 to 32	187	195	419	174	182	439	447
33 to 34	195	203	435	182	190	447	455
35 to 37	300	312	676	280	292	640	652
38 to 40	315	327	706	295	307	655	667
41 to 43	332	344	740	312	324	672	684
44 to 46	343	355	762	323	335	683	695
47 to 49	360	372	796	340	352	700	712
50 to 51	601	661	1,278	511	571	1,181	1,241
52 to 54	626	686	1,328	536	596	1,206	1,266
55 to 57	665	725	1,406	575	635	1,245	1,305
58 to 60	706	766	1,488	616	676	1,286	1,346
61 to 63	745	805	1,566	655	715	1,325	1,385
64 to 65	1,468	1,568	–	1,225	1,325	–	–
66 to 68	1,568	1,668	–	1,325	1,425	–	–
69 to 71	1,653	1,753	–	1,410	1,510	–	–
72 to 74	1,753	1,853	–	1,520	1,620	–	–
75 to 77	2,360	2,460	–	1,970	2,070	–	–
78 to 80	2,430	2,530	–	2,020	2,120	–	–
81 to 83	2,570	2,670	–	2,180	2,280	–	–
84 to 85	2,725	2,845	–	2,310	2,430	–	–
86 to 88	2,870	2,990	–	2,455	2,575	–	–
89 to 90	3,070	3,190	–	2,655	2,775	–	–
91 to 92	3,155	3,275	–	2,740	2,860	–	–
93 to 94	3,255	3,375	–	2,840	2,960	–	–
95 to 98	4,350	4,500	–	3,925	4,075	–	–
99 to 102	4,675	4,825	–	4,250	4,400	–	–
103 to 106	5,300	5,450	–	4,875	5,025	–	–
107 to 110	5,800	5,950	–	5,350	5,500	–	–

■ Based on 3'-0" C - C rod dimension and 8" total travel

