

Bit Holders

1/4" Female Square Drive



Part Number	Overall Length		
	In.	mm	
825	1	25	For 1/4" hex inserts
M-825	2 9/32	58	For 1/4" hex inserts; magnetic
820	23/32	18	For 1/4" square inserts

3/8" Female Square Drive




Part Number	Overall Length		
	In.	mm	
838	1 1/2	38	For 1/4" hex inserts
M-838	2 23/32	69	For 1/4" hex inserts; magnetic
835	1 1/2	38	For 5/16" hex inserts
M-835	2 3/4	70	For 5/16" hex inserts; magnetic
830	1 1/2	38	For 5/16" square inserts

1/2" Female Square Drive



Part Number	Overall Length		
	In.	mm	
858	1 3/4	45	For 1/4" hex inserts
M-858	2 3/4	70	For 1/4" hex inserts; magnetic
855	1 3/4	45	For 5/16" hex inserts
M-855	2 3/4	70	For 5/16" hex inserts; magnetic
850	1 3/4	45	For 5/16" square inserts

Bit Holders/Adapters with Set Screw or Thru Hole



Set Screw Lock	Part Number		Hex Opening (A) In.	Square Drive (B) In.	Overall Length (C)		Body Diameter (D)		Opening Depth (E)	
	Spring Pin Retainer	Spring Pin Only			In.	mm	In.	mm	In.	mm
	SC-108	-	-	1/4	1/4	1 1/4	32	3/4	19	5/8 16
	SC-308	-	-	1/4	3/8	1 1/2	38	3/4	19	5/8 16
	SC-508	-	-	1/4	1/2	1 1/2	38	7/8	22	5/8 16
	SC-114	-	-	7/16	1/4	1	25	3/4	19	17/32 13
	SC-314	RP-314	21-S-156-0750	7/16	3/8	1 3/8	35	3/4	19	17/32 13
	SC-514	RP-514	21-S-156-0937	7/16	1/2	1 5/8	41	15/16	24	17/32 13
	SC-614	RP-614	21-S-156-0375	7/16	5/8	1 3/4	46	1 1/4	32	17/32 13
	SC-520	RP-520	21-S-187-1125	5/8	1/2	1 1/2	38	1 1/8	29	11/16 17
	SC-620	RP-620		5/8	5/8	1 1/2	38	1 1/4	32	11/16 17
	SC-720	RP-720	21-S-187-1500	5/8	3/4	1 11/16	43	1 1/2	38	11/16 17
	SC-820	RP-820	21-S-187-1375	5/8	1	2 1/8	54	2 1/8	54	11/16 17
	SC-724	RP-724	21-S-187-1500	3/4	3/4	2	51	1 5/8	42	7/8 22
	SC-728	RP-728	21-S-187-1625	7/8	3/4	2	51	1 5/8	42	57/64 23
	SC-828	RP-828	21-S-187-1625	7/8	1	2 1/8	54	2 1/8	54	5/8 23

Note: Use SC and RP bit holders with socket head inserts (page 36) and pipe plug inserts (page 40). Can be used with power bits.