



Certificate of Compliance

Certificate: 2646937 (112384_0_000)

Master Contract: 187265

Project: 70051388

Date Issued: 2016-01-11

Issued to: Apollo Valves (Conbraco Industries, Inc.)
1418 S Pearl St
Pageland, South Carolina 29728
USA

Attention: Stephen Vollentine

The products listed below are eligible to bear the CSA Mark shown



Issued by: *James Sekerak*
James Sekerak

PRODUCTS

CLASS - C337110 - VALVES (GAS)-Lever Operated Non-Lubricated Shutoff

For details related to rating, size, configuration, etc. reference should be made to the CSA Certification Record or the descriptive report.

For Use with Natural, Mfd., Mixed, Liquefied Petroleum or Propane Gases and LP Gas-Air Mixtures

Straight Through

Model Number

76-100 Series

- 76-10101A, Rated Pressure: 125 psi, Inlet Size: ¼"
- 76-102-01A, Rated Pressure: 125 psi, Inlet Size: 3/8"
- 76-103-01A, Rated Pressure: 125 psi, Inlet Size: ½"
- 76-104-01A, Rated Pressure: 125 psi, Inlet Size: ¾"
- 76-105-01A, Rated Pressure: 125 psi, Inlet Size: 1"
- 76-106-01, Rated Pressure: 125 psi, Inlet Size: 1-1/4"
- 76-107-01, Rated Pressure: 125 psi, Inlet Size: 1-1/2"
- 76-108-01, Rated Pressure: 125 psi, Inlet Size: 2"
- 76-109-01, Rated Pressure: 125 psi, Inlet Size: 2-1/2"
- 76-100-01, Rated Pressure: 125 psi, Inlet Size: 3"



Certificate: 2646937
Project: 70051388

Master Contract: 187265
Date Issued: 2016-01-11

76F-100 Series

- 76F-101-(01,27), Rated Pressure: 125 psi, Inlet Size: 1/4"
- 76F-102-(01,27), Rated Pressure: 125 psi, Inlet Size: 3/8"
- 76F-103-(01,27)A, Rated Pressure: 125 psi, Inlet Size: 1/2"
- 76F-104-(01,27)A, Rated Pressure: 125 psi, Inlet Size: 3/4"
- 76F-105-(01,27)A, Rated Pressure: 125 psi, Inlet Size: 1"
- 76F-106-(01,27)A, Rated Pressure: 125 psi, Inlet Size: 1-1/4"
- 76F-107-(01,27)A, Rated Pressure: 125 psi, Inlet Size: 1-1/2"
- 76F-108-(01,27)A, Rated Pressure: 125 psi, Inlet Size: 2"
- 76F-100-(01,27)A, Rated Pressure: 125 psi, Inlet Size: 3"

APPLICABLE REQUIREMENTS

CSA/CAN 3.16-M88 (R-2014) – Lever Operated Non-Lubricated Gas Shut-Off Valves



Supplement to Certificate of Compliance

Certificate: 2646937 (112384_0_000)

Master Contract: 187265

*The products listed, including the latest revision described below,
are eligible to be marked in accordance with the referenced Certificate.*

Product Certification History

Project	Date	Description
70051388	2016-01-11	Addition of valve options to Model Series 76 and 76F.
70048116	2015-10-19	Addition of Model 76F, Size 3-inch.
70020384	2015-02-12	Addition of locking handle option "-27" to Model Series 76F-100. Addition of Figures 82 to 90.
2646937	2013-10-16	Original certification of 76-100 Series and 76F-100 Series to CAN 3.16-M88. Addition of Figures 1 to 81.

MASTER CONTRACT: 187265
REPORT: 2646937
PROJECT: 70051388

Date Issued: January 11, 2016

The following options are available to all sizes except where indicated for Model Series 76:

Suffix	Option
-02	Stem Grounded
-04	2.25" Stem Extension
-07	Steel Tee Handle
-08	90° Reversed Stem
-14	Side Vented Ball (Uni-Directional)
-15	Steel Wheel Handle
-16	Vertical Chain Lever
-19	Pad-Locking Devices
-21	UHMWPE Trim (Non-PTFE)
-24	Graphite Packing
-27	SS Latch-Lock Handle and SS Nut
-30	Cam-Lock Handle and Grounded
-32	SS Tee Handle And Nut
-35	PTFE Trim
-39	SS Hi-Rise Locking Wheel Handle, SS Nut
-40	Cyl-Loc and Grounded
-44	Seal Welded
-45	Less Lever And Nut
-46	SS Lock Closed Only
-47	SS Latch-Lock Oval Handle
-48	SS Oval Handle (No Latch) & Nut
-49	No Lubrication. Assembled Dry.
-50	2.25" Locking Stem Extension
-56	Multifill Seats & Packing
-57	Oxygen Cleaned
-58	Chain Lever - Horizontal
-60	Grounded Ball And Stem
-64	250 psi SWP (Steam Working Pressure)

MASTER CONTRACT: 187265
REPORT: 2646937
PROJECT: 70051388

Date Issued: January 11, 2016

The following options are available to all sizes except where indicated for Model Series **76F**:

Suffix	Option
-02	Stem Grounded
-04	2.25" Stem Extension
-08	90° Reversed Stem
-11	Therma-Seal™ Insulating Tee Handle
-14	Side Vented Ball (Uni-Directional)
-24	Graphite Packing
-27	SS Latch-Lock Handle and SS Nut
-30	Cam-Lock Handle and Grounded
-32	SS Tee Handle And Nut
-39	SS Hi-Rise Locking Wheel Handle, SS Nut
-40	Cyl-Loc and Grounded
-45	Less Lever And Nut
-46	SS Lock Closed Only
-47	SS Latch-Lock Oval Handle
-48	SS Oval Handle (No Latch) & Nut
-56	Multifill Seats & Packing
-60	Grounded Ball And Stem