

SHC Flexible Fixture Hangers

Outlet Box Mounted Series

UNILETS® for Use with Threaded Rigid Metal Conduit and IMC.

NEC/CEC:

Listed for Ordinary (Unclassified) Locations

Applications

- Designed for suspension of HID, fluorescent and incandescent lighting fixtures.
- SHC fixture hanger covers for mounting to 3-1/4" and 4" octagonal boxes and 4" square boxes.

Features

- Protect fixture against wind and vibration damage.
- Cushion type for added protection where lighting fixtures are subjected to vibration.
- Ball type swivel joint permits 20° swing from vertical.
- Support fixtures with a maximum weight of 22.7 kg (50 lbs).

Standard Materials

- Steel and malleable iron

Standard Finishes

- Malleable iron and steel parts: zinc electroplate and clear chromate

NEC/CEC Certifications and Compliances

- CSA Certified: 065180
- UL Listed: E2527
- UL Standard: 514A



8438R



8458R

Illustrated Features



Ball Type Swivel Fixture Hanger Covers shown with octagonal and with square stamped steel outlet boxes.

	Fixture Stem Size (Inches)	Length A mm (in)	Support Weight kg (lbs)	Catalog Number
SHC Ball Type Swivel Hanger Covers — Permit 20° swing from vertical				
For 3-1/4" and 4" Octagonal Boxes				
	1/2	44.5 (1.75)	22.5 (50)	8438R
	3/4	50.8 (2.00)	22.5 (50)	8436R
For 4" Square Boxes				
	1/2	44.5 (1.75)	22.5 (50)	8458R
	3/4	50.8 (2.00)	22.5 (50)	8456R

POLES/HANGERS: NEC/CEC ORDINARY LOCATION FLEXIBLE FIXTURE HANGERS

Appleton®