

ACSEW Control Operators: Pilot Light Components

Explosionproof

NEC/CEC:
 Class I, Division 1 and 2, Groups B, C, D
 Class II, Division 1 and 2, Groups E, F, G
 Class III
 NEMA 4, 7BCD, 9EFG

NEC/CEC — cULus Optional:
 Class I, Division 1 and 2, Groups B, C, D
 Class II, Division 1 and 2, Groups E, F, G
 Class III
 NEMA 4, 7BCD, 9EFG

Catalog Numbering Guide

AE
 NEC/CEC Certified
 Appleton Explosionproof

PL
 Pilot Light

G
 Guard:
 Omit for Standard Version
 (no guard)

1
 Voltage:
 1 - 120 Vac Pigtail
 2 - 240/120 Vac Transformer
 3 - 120/6 Vac Transformer
 4 - 480/120 Vac Transformer
 5 - 600/120 Vac Transformer
 6 - 6 Vac/Vdc Pigtail
 7 - 12 Vac/Vdc Pigtail
 8 - 24 Vac/Vdc Pigtail
 9 - 48 Vac/Vdc Pigtail

A
 Color:
 A - Amber
 B - Blue
 C - Clear
 R - Red
 G - Green

L
 Long Barrel:
 Omit for Short Barrel



Voltage	Lens Color	Pilot Light Catalog Number		Guarded Pilot Light Catalog Number	
		Short Barrel	Long Barrel	Short Barrel	Long Barrel
120 Vac/Vdc Pigtail ①	Amber	AEPL1A	AEPL1A-L	AEPLG1A	AEPLG1A-L
	Red	AEPL1R	AEPL1R-L	AEPLG1R	AEPLG1R-L
	Green	AEPL1G	AEPL1G-L	AEPLG1G	AEPLG1G-L
	Clear	AEPL1C	AEPL1C-L	AEPLG1C	AEPLG1C-L
	Blue	AEPL1B	AEPL1B-L	AEPLG1B	AEPLG1B-L
240 Vac Transformer w/120 Vac Lamp ①	Amber	AEPL2A	AEPL2A-L	AEPLG2A	AEPLG2A-L
	Red	AEPL2R	AEPL2R-L	AEPLG2R	AEPLG2R-L
	Green	AEPL2G	AEPL2G-L	AEPLG2G	AEPLG2G-L
	Clear	AEPL2C	AEPL2C-L	AEPLG2C	AEPLG2C-L
	Blue	AEPL2B	AEPL2B-L	AEPLG2B	AEPLG2B-L
120 Vac Transformer w/6 Vac Lamp	Amber	AEPL3A	AEPL3A-L	AEPLG3A	AEPLG3A-L
	Red	AEPL3R	AEPL3R-L	AEPLG3R	AEPLG3R-L
	Green	AEPL3G	AEPL3G-L	AEPLG3G	AEPLG3G-L
	Clear	AEPL3C	AEPL3C-L	AEPLG3C	AEPLG3C-L
	Blue	AEPL3B	AEPL3B-L	AEPLG3B	AEPLG3B-L

① For LED version, add suffix **-LED**. For LED versions 120 Vac only, and 12/24 Vdc only.

NOTE: Use long barrel devices on enclosure applications with cover thickness exceeding 22.225 mm (0.875"). For legend plates, see Options, Accessories and Nameplates. All Operators are 3/4" NPSM.

CONTROLS: NEC/CEC EXPLOSIONPROOF/FLAMEPROOF CONTROL STATIONS AND SWITCHES

APPLETON