

ACSEW Control Operators: Pilot Light Components

Explosionproof

NEC/CEC:
 Class I, Division 1 and 2, Groups B, C, D
 Class II, Division 1 and 2, Groups E, F, G
 Class III
 NEMA 4, 7BCD, 9EFG

NEC/CEC — cULus Optional:
 Class I, Division 1 and 2, Groups B, C, D
 Class II, Division 1 and 2, Groups E, F, G
 Class III
 NEMA 4, 7BCD, 9EFG

ATEX/IECEX — Optional ①:
 Zone 1 and 2 – 21 and 22
 ② II 2 GD
 IP66 – IK10

Catalog Numbering Guide

AE
 NEC/CEC Certified
 Appleton Explosionproof

PL
 Pilot Light

G
 Guard:
 Omit for Standard Version
 (no guard)

1
 Voltage:
 1 - 120 Vac Pigtail
 2 - 240/120 Vac Transformer
 3 - 120/6 Vac Transformer
 4 - 480/120 Vac Transformer
 5 - 600/120 Vac Transformer
 6 - 6 Vac Pigtail
 7 - 12 Vac Pigtail
 8 - 24 Vac Pigtail
 9 - 48 Vac Pigtail

A
 Color:
 A - Amber
 B - Blue
 C - Clear
 R - Red
 G - Green

L
 Long Barrel:
 Omit for Short Barrel



Standard



Guarded

Voltage	Lens Color	Pilot Light Catalog Number		Guarded Pilot Light Catalog Number	
		Short Barrel	Long Barrel	Short Barrel	Long Barrel
120 Vac/Vdc Pigtail	Amber	AEPL1A ②	AEPL1A-L ②	AEPLG1A ②	AEPLG1A-L ②
	Red	AEPL1R ②	AEPL1R-L ②	AEPLG1R ②	AEPLG1R-L ②
	Green	AEPL1G ②	AEPL1G-L ②	AEPLG1G ②	AEPLG1G-L ②
	Clear	AEPL1C ②	AEPL1C-L ②	AEPLG1C ②	AEPLG1C-L ②
	Blue	AEPL1B ②	AEPL1B-L ②	AEPLG1B ②	AEPLG1B-L ②
240 Vac Transformer w/120 Vac Lamp	Amber	AEPL2A ③	AEPL2A-L ③	AEPLG2A ③	AEPLG2A-L ③
	Red	AEPL2R ③	AEPL2R-L ③	AEPLG2R ③	AEPLG2R-L ③
	Green	AEPL2G ③	AEPL2G-L ③	AEPLG2G ③	AEPLG2G-L ③
	Clear	AEPL2C ③	AEPL2C-L ③	AEPLG2C ③	AEPLG2C-L ③
	Blue	AEPL2B ③	AEPL2B-L ③	AEPLG2B ③	AEPLG2B-L ③
120 Vac Transformer w/6 Vac Lamp	Amber	AEPL3A ③	AEPL3A-L ③	AEPLG3A ③	AEPLG3A-L ③
	Red	AEPL3R ③	AEPL3R-L ③	AEPLG3R ③	AEPLG3R-L ③
	Green	AEPL3G ③	AEPL3G-L ③	AEPLG3G ③	AEPLG3G-L ③
	Clear	AEPL3C ③	AEPL3C-L ③	AEPLG3C ③	AEPLG3C-L ③
	Blue	AEPL3B ③	AEPL3B-L ③	AEPLG3B ③	AEPLG3B-L ③

① Ordering a product with any ATEX Certification nulls the UL, CSA and cULus Certifications.
 ② For pilot light with ATEX Certification place an X suffix at the end of the catalog number; example: AEPL1AX.
 ③ Not available with ATEX Certification.

NOTE: Use long barrel devices on enclosure applications with cover thickness exceeding 22.225 mm (0.875").
 For legend plates, see Options, Accessories and Nameplates. All Operators are 3/4" NPSM.

CONTROL S: NEC/CEC, ATEX/IECEX EXPLOSIONPROOF/FLAMEPROOF CONTROL STATIONS AND SWITCHES

APPLETON