

# ACSEW Miniature Control Operators

## Explosionproof

### NEC/CEC:

Class I, Division 1 and 2, Groups B, C, D  
Class II, Division 1 and 2, Groups E, F, G  
Class III  
NEMA 4, 7BCD, 9EFG

### NEC/CEC — cULus Optional:

Class I, Division 1 and 2, Groups B, C, D  
Class II, Division 1 and 2, Groups E, F, G  
Class III  
NEMA 4, 7BCD, 9EFG

### ATEX/IECEX — Optional ①:

Zone 1 and 2 – 21 and 22  
II 2 GD  
IP66 – IK10

### Features

- Installation centers reduced to 1" centers.
- Allows selection of smaller enclosures.
- 3/8 - 16 thread.
- Stainless steel actuator shaft.
- Solid silver contacts rated 6 Amps at 125 Vac, 3 Amps at 250 Vac.



Contact Configuration	Catalog Number
DPDT Maintained	AEPMOB-3
DPDT Momentary	AEPMOB-4

CONTROLS: NEC/CEC, ATEX/IECEX EXPLOSIONPROOF/FLAMEPROOF CONTROL STATIONS AND SWITCHES

APPLETON™

① Ordering a product with any ATEX Certification nulls the UL, CSA and cULus Certifications.

NOTE: Use long barrel devices on enclosure applications with cover thickness exceeding 22.225 mm (0.875").  
For legend plates, see Options, Accessories and Nameplates. Miniature operators are NOT 3/4" NPSM.