

# ACSEW Control Operators: Mushroom Head Push Button Components

## Maintained Contact. Explosionproof

### NEC/CEC:

Class I, Division 1 and 2, Groups B, C, D  
Class II, Division 1 and 2, Groups E, F, G  
Class III  
NEMA 4, 7BCD, 9EFG

### NEC/CEC — cULus Optional:

Class I, Division 1 and 2, Groups B, C, D  
Class II, Division 1 and 2, Groups E, F, G  
Class III  
NEMA 4, 7BCD, 9EFG

### ATEX/IECEX — Optional ①:

Zone 1 and 2 – 21 and 22  
II 2 GD  
IP66 – IK10

### Catalog Numbering Guide

**AE**  
NEC/CEC Certified  
Appleton Explosionproof

**P**  
Push Button

**MC**  
Mushroom Head, Maintained

**B**  
Color:  
B - Black  
R - Red  
G - Green

**A**  
Contact Arrangement:  
A - 1 NO  
B - 2 NO  
C - 1 NC  
D - 2 NC  
E - 1 NO and 1 NC  
F - 2 NO and 2 NC

**L**  
Long Barrel:  
Omit for Short Barrel



Contacts ②	Lens Color	Catalog Number	
		Short Barrel	Long Barrel
1 NO	Black	AEPMCBA	AEPMCBA-L
1 NO	Red	AEPM CRA	AEPM CRA-L
1 NO	Green	AEPM CGA	AEPM CGA-L
2 NO	Black	AEPM CBB	AEPM CBB-L
2 NO	Red	AEPM CRB	AEPM CRB-L
2 NO	Green	AEPM CGB	AEPM CGB-L
1 NC	Black	AEPM CBC	AEPM CBC-L
1 NC	Red	AEPM CRC	AEPM CRC-L
1 NC	Green	AEPM CGC	AEPM CGC-L

Contacts ②	Lens Color	Catalog Number	
		Short Barrel	Long Barrel
2 NC	Black	AEPM CBD	AEPM CBD-L
2 NC	Red	AEPM CRD	AEPM CRD-L
2 NC	Green	AEPM CGD	AEPM CGD-L
1 NO and 1 NC	Black	AEPM CBE	AEPM CBE-L
1 NO and 1 NC	Red	AEPM CRE	AEPM CRE-L
1 NO and 1 NC	Green	AEPM CGE	AEPM CGE-L
2 NO and 2 NC	Black	AEPM CBF	AEPM CBF-L
2 NO and 2 NC	Red	AEPM CRF	AEPM CRF-L
2 NO and 2 NC	Green	AEPM CGF	AEPM CGF-L

① Ordering a product with any ATEX Certification nulls the UL, CSA and cULus Certifications.

② NO = Normally Open; NC = Normally Closed.

NOTE: Use long barrel devices on enclosure applications with cover thickness exceeding 22.225 mm (0.875"). For legend plates, see Options, Accessories and Nameplates. All Operators are 3/4" NPSM.