

ACSEW Control Operator Accessories

Explosionproof

NEC/CEC:
 Class I, Division 1 and 2, Groups B, C, D
 Class II, Division 1 and 2, Groups E, F, G
 Class III
 NEMA 4, 7BCD, 9EFG

NEC/CEC — cULus Optional:
 Class I, Division 1 and 2, Groups B, C, D
 Class II, Division 1 and 2, Groups E, F, G
 Class III
 NEMA 4, 7BCD, 9EFG

ATEX/IECEX — Optional ①:
 Zone 1 and 2 – 21 and 22
 ② II 2 GD
 IP66 – IK10

	Item	Description	Catalog Number
	360° Rotating Shaft	Manual operated shaft used for devices requiring external adjustment. The shaft is 6.35 mm (0.25") diameter and is provided with a coupling to compensate for misalignment.	ARO250C
	Standard Reset Button	Six-inch length can be field modified for specific length. Suitable for use in Class I, Groups B, C and D applications.	AEPRS
	Miniature Reset Button	Six-inch length can be field modified for specific length. Suitable for use in Class I, Groups B, C and D applications. 3/8 - 16 Threads.	AEPRM ②
	Weather Cap For Push Button Devices	Field attachable weather cap snaps on easily without the use of adhesives. Black Green Red	PBCAPB PBCAPG PBCAPR
	Plug	3/4" NPSM to plug unused openings.	AA-9400
 <p data-bbox="237 1629 285 1650">AP02</p> <p data-bbox="488 1692 537 1713">AP01</p>	Potentiometer Operator	Operator for use with potentiometers having a 6.35 mm (0.25") diameter by 22.225 mm (0.875") long shaft. The operator is furnished with a control knob and dial plate marked 0 to 100. Long bushing for applications where enclosure cover thickness is greater than 22.225 mm (0.875").	AP01 AP02

CONTROL STATIONS: NEC/CEC, ATEX/IECEX EXPLOSIONPROOF/FLAMEPROOF CONTROL STATIONS AND SWITCHES



① Ordering a product with any ATEX Certification nulls the UL, CSA and cULus Certifications.
 ② Not available with ATEX Certification.

NOTE: Use long barrel devices on enclosure applications with cover thickness exceeding 22.225 mm (0.875"). For legend plates, see Options, Accessories and Nameplates. All Operators are 3/4" NPSM.