

AGUB and NGUB Instrument and Meter Enclosures

Explosionproof, Dust-Ignitionproof

Furnished with aluminum body and solid or window cover.

NEC/CEC:

Class I, Division 1 and 2, Groups B, C, D

Class II, Division 1 and 2, Groups E, F, G

Class III

NEMA 4, 4X, 7BCD, 9EFG

Application

- To pull or splice wires and/or to mount and enclose electrical devices in hazardous locations.

Features

- Precision threaded flame path between box and cover.
- O-ring gasket provided to seal out moisture, dust, oil, dirt etc. for interior and exterior locations.
- Cast mounting feet provided on all enclosures.
- Large cover opening for easy access.
- Available with solid or window covers.

Standard Materials

- Bodies: copperfree (4/10 of 1% max.) aluminum
- AGUB and NGUB covers: copperfree (4/10 of 1% max.) aluminum
- AGUBSW and NGUBSW covers: copperfree (4/10 of 1% max.) aluminum and glass
- O-ring: neoprene

Standard Finishes

- Corrosion resistant gray powder coat epoxy standard

NEC/CEC Certifications and Compliances

- UL Standard: UL 1203
- cULus Classified: E84577
- CSA Standard: C22.2 No. 25, C22.2 No. 30
- CSA Certified: 020945



AGUB and NGUB Instrument and Meter Enclosures

Explosionproof, Dust-Ignitionproof

NEC/CEC:

Class I, Division 1 and 2, Groups B, C, D

Class II, Division 1 and 2, Groups E, F, G

Class III

NEMA 4, 4X, 7BCD, 9EFG

ENCLOSURES AND JUNCTION BOXES: NEC/CEC EXPLOSIONPROOF ENCLOSURES

Mounting Plates — Standard

Appleton			O-Z/Gedney		
Catalog Number		Use With	Catalog Number		Use With
Aluminum	Galvanized Steel	Box Catalog Number	Aluminum	Galvanized Steel	Box Catalog Number
AMPA-443	AMPG-443	AGUB-443A	NMPA-443	NMPG-443	NGUB-443A
AMPA-555	AMPG-555	AGUB-555A	NMPA-555	NMPG-555	NGUB-555A
AMPA-664	AMPG-664	AGUB-664A	NMPA-664	NMPG-664	NGUB-664A
AMPA-976	AMPG-976	AGUB-976A	NMPA-976	NMPG-976	NGUB-976A
AMPA-984	AMPG-984	AGUB-984A	NMPA-984	NMPG-984	NGUB-984A
AMPA-1093	AMPG-1093	AGUB-1093A	NMPA-1093	NMPG-1093	NGUB-1093A
AMPA-10105	AMPG-10105	AGUB-10105A	NMPA-10105	NMPG-10105	NGUB-10105A
AMPA-10106	AMPG-10106	AGUB-10106A	NMPA-10106	NMPG-10106	NGUB-10106A
AMPA-10108	AMPG-10108	AGUB-10108A	NMPA-10108	NMPG-10108	NGUB-10108A
AMPA-12128	AMPG-12128	AGUB-12128A	NMPA-12128	NMPG-12128	NGUB-12128A
AMPA-121212	AMPG-121212	AGUB-121212A	NMPA-121212	NMPG-121212	NGUB-121212A

Mounting Plates — 90°

Appleton			O-Z/Gedney		
Catalog Number		Use With	Catalog Number		Use With
Aluminum	Galvanized Steel	Box Catalog Number	Aluminum	Galvanized Steel	Box Catalog Number
AMD-4-664A	AMD-4-664G	AGUB-664A	NMD-4-664A	NMD-4-664G	NGUB-664A
AMD-10-664A	AMD-10-664G	AGUB-664A	NMD-10-664A	NMD-10-664G	NGUB-664A
AMD-6-984A	AMD-6-984G	AGUB-984A	NMD-6-984A	NMD-6-984G	NGUB-984A
AMD-8-1093A	AMD-8-1093G	AGUB-1093A	NMD-8-1093A	NMD-8-1093G	NGUB-1093A
AMD-10-10105A	AMD-10-10105G	AGUB-10105A	NMD-10-10105A	NMD-10-10105G	NGUB-10105A

Replacement Flat Covers

Appleton		O-Z/Gedney	
Catalog Number	Use With Box Catalog Number	Catalog Number	Use With Box Catalog Number
AFC-443A	AGUB-443A	NFC-443A	NGUB-443A
AFC-555A	AGUB-555A	NFC-555A	NGUB-555A
AFC-664A	AGUB-664A	NFC-664A	NGUB-664A
AFC-976A	AGUB-976A	NFC-976A	NGUB-976A
AFC-984A	AGUB-984A	NFC-984A	NGUB-984A
AFC-1093A	AGUB-1093A	NFC-1093A	NGUB-1093A
AFC-10105A	AGUB-10105A	NFC-10105A	NGUB-10105A
AFC-1010A	AGUB-10106/8A	NFC-1010A	NGUB-10106/8A
AFC-1212A	AGUB-12128/12A	NFC-1212A	NGUB-12128/12A

NEMA 4X Breather/Drain Fittings

Description	Suffix Factory-Installed ①	Catalog Number Field-Installed
Drain Fitting	NGK-04	DRNB4X
Breather Fitting	NGK-10	BRTB4X

① Drilled and tapped installation included.