

Code•Master™ 2 HID Factory Sealed Floodlights

Marine (Outside Type). Explosionproof

Integrally Ballasted. 150 W, 250 W, 400 W HPS; 175 W, 250 W, 400 W PSMH; 175 W, 250 W, 400 W MH. Mogul Base.

NEC:
Class 1, Division 1 and 2, Groups C, D
Marine Type Electric Fixtures
Outside Type (Salt Water)

CEC:
Class I, Division 1 and 2, Groups B, C, D
Class II, Division 1, Groups E, F, G
Class II, Division 2, Groups F, G
Class III
CSA 4X

	Description	Catalog Number
	Box has 1/2" opening for threading to Flexible Coupling, and two 3/4" conduit openings (3/4 – 14NPT) and is furnished with one 3/4" close-up plug. Locking screw for horizontal adjustment. Trunnion bolts furnished. Aluminum, gray epoxy finish.	AF-JB
	Threads onto 2" pipe with tapered threads (2-11 – 1/2 NPT). Includes floodlight trunnion bolts. Locking screw for horizontal floodlight adjustment. Aluminum, gray epoxy finish.	AF-SF
	Has 180° horizontal adjustment – degree-marked. Facilitates mounting floodlight to crossarm or other flat surface, or to G-AM-8-WB Pole/Wall Mounting Bracket (see photo below). Includes floodlight trunnion bolts. Malleable iron, plated, chromate sealed, architectural bronze EPOXY finish.	G-AM-8-CA
 <p>Standard and Deep Dome 30° Angle</p>	Standard Dome Deep Dome 30° Angle	CMR-4ST CMR-4DD CMR-4AN
		CMR-4HB
	Connects to 3/4" Fixture Unit hub (3/4 – 14 NPT) and to 1/2" Junction Box or Pole-Top Accessory opening (1/2 – 14 NPT).	AF-EXL
Quartz Emergency Lamp for Pulse Start Metal Halide and High Pressure Sodium Fixtures Fixtures can be supplied with a socket to accept a 150 W or 250 W, 120 V quartz lamp. This D.C. bayonet base socket is in addition to the standard lamp socket, independent of the lighting fixture voltage. <p style="text-align: right;">Add Suffix-E</p>		
HPS Smart Hot Restrike Smart Hot Restrike will immediately restrike an HPS lamp when power is restored after a momentary power interruption. The smart function removes the hot restrike ignitor from the circuit if the lamp burns out or is removed from the socket. Eliminates starter failures caused by prolonged operation with cycling or failing lamps and simplifies finding their location, reducing maintenance and repair costs. <p style="text-align: right;">Add Suffix -SR</p>		
HPS Hot Restrike Restrikes HPS lamp immediately when power is restored after a momentary power interruption. <p style="text-align: right;">Add Suffix -R</p>		
HPS Smart Starter Smart Starter for HPS and PSMH fixtures. Incorporates a 1-1/2-minute timer and performs as a conventional starter to normally start lamp. Removes itself from circuit if lamp burns out or is removed from socket. Eliminates starter failures caused by prolonged operation with cycling or failing lamps and simplifies finding their location, reducing maintenance and repair costs. <p style="text-align: right;">Add Suffix -S</p>  <p>Optional for all fixture watts G-AM-8-CA Crossarm Mounting Bracket Shown with G-AM-8-WB Pipe/Wall Mounting Bracket. The G-AM-8-WB bracket is not furnished with fixtures.</p>		

Appleton

HID/FLOODLIGHT: NEC/CEC EXPLOSIONPROOF