

AL Ball and Cushion Flexible Fixture Hangers

UNILETS® for Use with Threaded Rigid Metal Conduit and IMC. Ball Joint Permits 20° Swing.

NEC:
Listed for Ordinary (Unclassified) Locations

Applications

- Designed for suspension of HID, fluorescent and incandescent lighting fixtures.
- Functions as combination conduit outlet box and hanger.

Features

- Protects fixture against wind and vibration damage.
- Cushion type for added protection where lighting fixtures are subjected to vibration.
- Dual function—conduit outlet box and fixture hanger.
- Choice of ball or cushion type.
- Swivel joint construction—allows 20° swing from vertical.
- Cushion style, with conical spring, supports up to 54 kg (120 lbs).
- Cushion type has setscrew for locking fixture stem.
- Fixture and hanger stem can be wired at work bench.
- Connection block available for convenient wiring of fixture leads.

Standard Materials

- Malleable iron with steel cover

Standard Finishes

- Malleable iron parts: triple-coat—(1) zinc electroplate, (2) chromate, and (3) epoxy powder coat
- Steel parts: zinc electroplate

NEC Certifications and Compliances

- UL Listed: E109438



ALA — Ball Hanger



ALC — Ball Hanger




ALL — Cushion Hanger



ALT — Cushion Hanger

Illustrated Features



Baymaster High Bay HID
Fixture Hanger

AL Ball and Cushion Flexible Fixture Hangers

UNILETS® for Use with Threaded Rigid Metal Conduit and IMC. Ball Joint Permits 20° Swing.

NEC:
Listed for Ordinary (Unclassified) Locations

	Conduit Size (Inches)	Fixture Stem Size (Inches)	Support Weight kg (lbs)	Catalog Number
ALA — Ball Hanger				
	1/2	1/2		ALA50-B
	3/4	1/2	112.5 (250)	ALA7550-B
	3/4	3/4	112.5 (250)	ALA75-B
ALA — Cushion Hanger — Furnished with a 3/4" to 1/2 reducer for 1/2" stems				
	1/2	3/4 or 1/2		ALA50-12
	3/4	3/4 or 1/2	1.4 to 5.4 (3 to 12)	ALA7575-12
	1/2	3/4 or 1/2		ALA50-48
	3/4	3/4 or 1/2	5.4 to 21.6 (12 to 48)	ALA7575-48
	1/2	3/4 or 1/2		ALA50-120
	3/4	3/4 or 1/2	21.6 to 54.0 (48 to 120)	ALA7575-120
ALC — Ball Hanger				
	1/2	1/2		ALC50-B
	3/4	1/2	112.5 (250)	ALC7550-B
	1	1/2		ALC1050-B
	3/4	3/4		ALC75-B
	1	3/4	112.5 (250)	ALC1075-B
ALC — Cushion Hanger — Furnished with a 3/4" to 1/2" reducer for 1/2" stems				
	1/2	3/4 or 1/2		ALC50-12
	3/4	3/4 or 1/2	1.4 to 5.4 (3 to 12)	ALC7575-12
	1	3/4 or 1/2		ALC1075-12
	1/2	3/4 or 1/2		ALC50-48
	3/4	3/4 or 1/2	5.4 to 21.6 (12 to 48)	ALC7575-48
	1	3/4 or 1/2		ALC1075-48
	1/2	3/4 or 1/2		ALC50-120
	3/4	3/4 or 1/2	21.6 to 54.0 (48 to 120)	ALC7575-120
	1	3/4 or 1/2		ALC1075-120