

ACSEW Cast Control Center Options and Accessories

Explosionproof, Dust-Ignitionproof

NEC/CEC:
 Class I, Division 1 and 2, Groups B, C, D
 Class II, Division 1 and 2, Groups E, F, G
 Class III
 NEMA 4, 7BCD, 9EFG

NEC/CEC – cULus Optional:
 Class I, Division 1 and 2, Groups B, C, D
 Class II, Division 1 and 2, Groups E, F, G
 Class III
 NEMA 4, 7BCD, 9EFG

ATEX/IECEX – Optional ①:
 Zone 1 and 2 – 21 and 22
 ② II 2 GD
 IP66 – IK10

Round Windows ③

Catalog Number	Description
AW5	3" Viewing Area, Round Group B
AW6	4" Viewing Area, Round Group B
AW7	5" Viewing Area, Round Group B
AW10	7" Viewing Area, Round Group B
AW12	9" Viewing Area, Round Group B

Circuit Breaker Operators

Catalog Number	Description
AV1W	150AF Circuit Breaker Mechanism
AV2W	250AF Circuit Breaker Mechanism

Options

Factory Installed Suffix	Field Installed Catalog Number	Description
AB	N/A	Set of 4 standoffs 1/2" high
BR	BRTB4X	Breather, NEMA 4X (includes outlet and installation)
DN	DRNB4X	Drain, NEMA 4X (includes outlet and installation)
EGS	N/A	External grounding stud 3/8"-16
G1	N/A	Gray Powder Coat Epoxy (outside)
G2	N/A	Gray Powder Coat Epoxy (inside and outside)
H		Hinges stainless steel
	AHOF12SS	Hinge Kit, 2 light duty SS hinges
	AHOF22SS	Hinge Kit, 2 heavy duty SS hinges
	AHOF23SS	Hinge Kit, 3 heavy duty SS hinges
K ②	N/A	Terminal blocks 600 Vac, 30 Amp (example: 5 points = 5K)
NP	N/A	Plastic nameplate, 2" x 4", 1/8" black letters on white surface, 3 lines max., specify legend.
NPSM75	N/A	3/4" NPSM Drill and Tap
Z	See Options and Accessories	Mounting pan

Mounting Hardware

Field Installed Catalog Number	Description
AMH1	1/4" - 20 x 1-1/4" Bolt, 1/4" - 20 Hex Nut, 1/4" Washers
AMH2	3/8" - 16 x 1-1/4" Bolt, 3/8" - 16 Hex Nut, 3/8" Washers
AMH3	7/16" - 14 x 1-3/4" Bolt, 7/16" - 14 Hex Nut, 7/16" Washers
AMH4	1/2" - 13 x 1-3/4" Bolt, 1/2" - 13 Hex Nut, 1/2" Washers
AMH5	1/2" - 13 x 2" Bolt, 1/2" - 13 Hex Nut, 1/2" Washers
AMH6	5/8" - 11 x 2" Bolt, 5/8" - 11 Hex Nut, 5/8" Washers
AMH7	1/2" - 13 x 1-1/4" Bolt, 1/2" - 13 Hex Nut, 1/2" Washers
AMH8	5/8" - 11 x 1-1/4" Bolt, 5/8" - 11 Hex Nut, 5/8" Washers

Drill and Tap Options

Symbol	Conduit Size (Inches – NPT)
A	1/2
B	3/4
C	1
D	1-1/4
E	1-1/2
F	2
G	2-1/2
H	3
J	3-1/2
K	4

Blind Tapped Holes

Suffix	Screw Size
BT1	#6 - 1/4"
BT2	5/16" - 1/2"

① Ordering a product with any ATEX Certification nulls the UL, CSA and cULus Certifications.

② Indicate number of points.

③ Not available with ATEX Certification.