

# Powerlite™ 30, 60, 100, and 150 Amp Replacement Interiors

600 Vac, 250 Vdc, 50-400 Hz

NEC/CEC:  
Listed for Ordinary (Unclassified) Locations  
NEMA 3, 4, 4X

PLUGS AND RECEPTACLES: NEC/CEC ORDINARY LOCATION

APPLETON™

## 30 Amp ①



Grounding Style	Wire/Pole	Receptacle	Plug	Receptacle	Plug
Style 1 (Shell Only)	2W, 2P	<b>ARI-3022</b>	<b>API-3022</b>	—	—
	3W, 3P	<b>ARI-3033</b>	<b>API-3033</b>	—	—
	4W, 4P	<b>ARI-3044</b>	<b>API-3044</b>	—	—
Style 2 (Shell and Extra Pole)	2W, 3P	—	—	<b>ARI-3023</b>	<b>API-3023</b>
	3W, 4P	—	—	<b>ARI-3034</b>	<b>API-3034</b>

## 60 Amp ①



Grounding Style	Wire/Pole	Receptacle	Plug	Receptacle	Plug
Style 1 (Shell Only)	2W, 2P	<b>ARI-6022</b>	<b>API-6022</b>	—	—
	3W, 3P	<b>ARI-6033</b>	<b>API-6033</b>	—	—
	4W, 4P	<b>ARI-6044</b>	<b>API-6044</b>	—	—
Style 2 (Shell and Extra Pole)	2W, 3P	—	—	<b>ARI-6023</b>	<b>API-6023</b>
	3W, 4P	—	—	<b>ARI-6034</b>	<b>API-6034</b>

## 100 and 150 Amp ①



Grounding Style	Wire/Pole	Receptacle	Plug	Receptacle	Plug
Style 1 (Shell Only)	2W, 2P	<b>ARI-1022</b>	<b>API-1022</b>	—	—
	3W, 3P	<b>ARI-1033</b>	<b>API-1033</b>	—	—
	4W, 4P	<b>ARI-1044</b>	<b>API-1044</b>	—	—
Style 2 (Shell and Extra Pole)	2W, 3P	—	—	<b>ARI-1023</b>	<b>API-1023</b>
	3W, 4P	—	—	<b>ARI-1034</b>	<b>API-1034</b>
150 Amp Style 2 (Shell and Extra Pole)	3W, 4P	—	—	<b>ARI-15034</b>	<b>API-15034</b>

① Pins and sleeves are not sold separately.