

# ASR Nonmetallic Interlocked Receptacles

## With Enclosed Disconnect Switch

600 Vac, 30 and 60 Amp, Fused and Non-Fused

NEC/CEC:  
NEMA 4X, 12



Amp	Type	Config.	Catalog Number
30	Non-Fused	3W 4P	ASR3034
	Fused		ASR3034F
60	Non-Fused	3W 4P	ASR6034
	Fused		ASR6034F

### Mating Powertite™ Plug



Type	Amp	AWG	Cable Range (inches)	Style of Cable	Config.	Mating Plug
Non-Metallic	30	12-6	.500 to 1.125	G,W,S, SO and STO	3W 4P	NMACP3034BC
	60	8-4	.500 to 1.375			NMACP6034BC
Metallic	30	12-6	.500 to 1.125	G,W,S, SO and STO	3W 4P	ACP3034BC
	60	8-4	.500 to 1.375			ACP6034BC

### Optional Auxiliary Contacts

Amps	Interlock Type	Fusible Catalog Number	Non-Fusible Catalog Number
30	1 N/O, 1 N/C	ASR30FDAUX	ASR30AUX
60	1 N/O	ASR60FDAUX-O	ASR60AUX
60	1 N/C	ASR60FDAUX-C	N/A

### Replacement Parts



Description	Catalog Number
30 Amp Cover	PTTC30
60 Amp Cover	PTTC60B

### Horsepower Ratings

Amp		Fusible — Single Phase				Non-Fused — Single Phase			
		208 Vac	240 Vac	480 Vac	600 Vac	208 Vac	240 Vac	480 Vac	600 Vac
30	Standard	—	1.5	3	—	5	5	10	10
	Maximum	5	5	7.5	—	—	—	—	—
60	Standard	—	3	5	—	10	10	20	30
	Maximum	7.5	7.5	15	—	—	—	—	—

  

Amp		Fusible — Three Phase				Non-Fused — Three Phase			
		208 Vac	240 Vac	480 Vac	600 Vac	208 Vac	240 Vac	480 Vac	600 Vac
30	Standard	—	3	5	7.5	10	10	20	20
	Maximum	7.5	7.5	15	20	—	—	—	—
60	Standard	7.5	7.5	15	15	20	20	40	50
	Maximum	15	15	30	50	—	—	—	—

PLUGS AND RECEPTACLES: NEC/CEC ORDINARY LOCATION

APPLETON™